





PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- 4、Contact Resistance: $10\text{m}\Omega$ Max
- 5、Insulation Resistance: $1000\text{m}\Omega$ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Wafer Nylon66, UL94V-0
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
A2004WV-02A	2.00	6.00
A2004WV-03A	4.00	8.00
A2004WV-04A	6.00	10.00
A2004WV-05A	8.00	12.00
A2004WV-06A	10.00	14.00
A2004WV-07A	12.00	16.00
A2004WV-08A	14.00	18.00
A2004WV-09A	16.00	20.00
A2004WV-10A	18.00	22.00
A2004WV-11A	20.00	24.00
A2004WV-12A	22.00	26.00
A2004WV-15A	28.00	32.00

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图	郑 弋			料号 PART NO.	A2004WV-NA		版本 REV.	A
			X.±0.25	X.*±2'	审核	2008、07、01			品名 TITLE	PHD直针座		页次 SHEET	1/1
			.X±0.20	.X*±1'	核准	2008、07、03			客户料号 CUTM. NO.				
			.XX±0.15	.XX*±0.5'		2008、07、05							
			.XXX±0.10	.XXX*±0.5'	单位 UNITS	MM	比例 SCALE	1:1					



PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- 4、Contact Resistance: $10\text{m}\Omega$ Max
- 5、Insulation Resistance: $1000\text{m}\Omega$ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Wafer Nylon66, UL94V-0
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
A2004WR-02A	2.00	6.00
A2004WR-03A	4.00	8.00
A2004WR-04A	6.00	10.00
A2004WR-05A	8.00	12.00
A2004WR-06A	10.00	14.00
A2004WR-07A	12.00	16.00
A2004WR-08A	14.00	18.00
A2004WR-09A	16.00	20.00
A2004WR-10A	18.00	22.00
A2004WR-11A	20.00	24.00
A2004WR-12A	22.00	26.00
A2004WR-15A	28.00	32.00

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图	郑 弋			料号 PART NO.	A2004WR-NA		版本 REV.	A
			X.±0.25	X.*±2'	审核	2008、07、01			品名 TITLE	PHD弯针座		页次 SHEET	1/1
			.X±0.20	.X'±1'	核准	2008、07、03			客户料号 CUTM. NO				
			.XX±0.15	.XX'±0.5'		2008、07、05							
			.XXX±0.10	.XXX'±0.5'	单位 UNITS	MM	比例 SCALE	1:1					