



技术指标:

1. 温度范围: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
2. 额定电压: 250V AC,DC.
3. 耐压: 1500V AC/minute.
4. 接触电阻: $\leq 20\text{m}\Omega$.
5. 绝缘电阻: $\geq 1000\text{M}\Omega$.
6. 额定电流: 5A AC,DC.

型号	CKT	A	B
WAFER-WBM4.2-02PJK-GB	2*1	0.00	5.50
WAFER-WBM4.2-04PJK-GB	2*2	4.20	9.70
WAFER-WBM4.2-06PJK-GB	2*3	8.40	13.90
WAFER-WBM4.2-08PJK-GB	2*4	12.60	18.10
WAFER-WBM4.2-10PJK-GB	2*5	16.80	22.30
WAFER-WBM4.2-12PJK-GB	2*6	21.00	26.50
WAFER-WBM4.2-14PJK-GB	2*7	25.20	30.70
WAFER-WBM4.2-16PJK-GB	2*8	29.40	34.90
WAFER-WBM4.2-18PJK-GB	2*9	33.40	39.10
WAFER-WBM4.2-20PJK-GB	2*10	37.80	43.30
WAFER-WBM4.2-22PJK-GB	2*11	42.00	47.50
WAFER-WBM4.2-24PJK-GB	2*12	46.20	51.70

MANUFACTURE DWG			 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: WBM4.2MM HOUSING	
DECIMALS:	ANGLES:	PAR	WAFER-WBM4.2-NPJK-GB	
X.X±0.30	X.*±5'	DWN		
X.XX±0.25	X.X'±1'	CHKD		
X.XXX±0.15		APVD		
CUSTOMER COPY		SCALE:A	UNIT:MM	
		SIZE:A4	SHEET:1F1	REV:A