



技术指标:

1. 温度范围:  $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$ .
2. 额定电压: 250V AC, DC.
3. 耐电压: 1500V AC/minute.
4. 接触电阻:  $\leq 20\text{m}\Omega$ .
5. 绝缘电阻:  $\geq 1000\text{M}\Omega$ .
6. 额定电流: 5A AC, DC.

型号	CKT	A	B
WAFER-WBM4.2-02PJK-GY	2*1	0.00	5.50
WAFER-WBM4.2-04PJK-GY	2*2	4.20	9.70
WAFER-WBM4.2-06PJK-GY	2*3	8.40	13.90
WAFER-WBM4.2-08PJK-GY	2*4	12.60	18.10
WAFER-WBM4.2-10PJK-GY	2*5	16.80	22.30
WAFER-WBM4.2-12PJK-GY	2*6	21.00	26.50
WAFER-WBM4.2-14PJK-GY	2*7	25.20	30.70
WAFER-WBM4.2-18PJK-GY	2*9	33.40	39.10
WAFER-WBM4.2-20PJK-GY	2*10	37.80	43.30
WAFER-WBM4.2-22PJK-GY	2*11	42.00	47.50
WAFER-WBM4.2-24PJK-GY	2*12	46.20	51.70

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: WBM4.2MM HOUSING
DECIMALS: X.X±0.30			PAR WAFER-WBM4.2-NPJK-GY
ANGLES: X.*±5'			DWN
X.XX±0.25			CHKD
X.XXX±0.15		APVD	SCALE: A UNIT: MM
		CUSTOMER COPY	SIZE: A4 SHEET: 1F1 REV: A