


-, MATERIAL:

1. Insulator: PBT+30% Glass Fiber
2. Contact: Brass
3. Contact Plated: Gold Flash over Tin Or Gold Plated Or Tin Plated
4. Shell: Steel, Nickel Plated

≡, SPECIFICATION:

1. Current Rating: 3 AMPS
2. Insulation Resistance: 100MΩ MIN. At 500VDC
3. Dielectric Strength: 500V for One minute
4. Operation Temperature: -55° C~+105° C.

\*【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】



RECOMMEND PCB LAYOUT (T=1.6)  
PCB TOLERANCE: ±0.05

|                                       |          |   |                         |
|---------------------------------------|----------|---|-------------------------|
| MANUFACTURE DWG                       |          |  东莞市讯普电子科技有限公司<br>DongGuan XunPu Electronics Co.,Ltd |                         |
| UNLESS OTHERWISE SPECIFIED TOLERANCES |          |    | TITLE:<br>DR9F双锁        |
|                                       |          |   | PAR<br>D-SUB-DR-9PCM-BB |
| DECIMALS:                             | ANGLES:  |   | DWN                     |
| X.X±0.30                              | X.*±5°   |   | CHKD                    |
| X.XX±0.25                             | X.X*±2°  | APVD  | SCALE N:A               |
| X.XXX±0.15                            | X.XX*±1° | CUSTOMER COPY   | UNIT:MM                 |
|                                       |          | SIZE:A4   | UNIT:MM                 |
|                                       |          | SHEET:1F1   | REV:A                   |