



Technical Index:

1. Temperature range:  $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$ .
2. Rated voltage: 250V DC/AC.
3. Rated current: 3.0A DC/AC.
4. Contact resistance:  $\leq 20\text{m}\Omega$ .
5. Dielectric withstanding voltage: 800V AC/minute.
6. Insulation resistance:  $\geq 1000\text{M}\Omega$ .
7. Apply to gauge: AWG#24~#28.

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: PHB2.0公头端子
DECIMALS:	ANGLES:		PAR WAFER-PHB2.0-DZ-G
X.X±0.30	X.*±5°		DWN
X.XX±0.25	X.X°±1°		CHKD
X.XXX±0.15		APVD	SCALE:A UNIT:MM
CUSTOMER COPY		SIZE:A4	SHEET:1F1
			REV:A