


- , MATERIAL:
1. Insulator: PBT+30%Glass Fiber
 2. Contact: Brass
 3. Contact Plated: Gold Flash over Tin Or Glod Plated Or Tin Plated
 4. Shell: Steel, Nickel Plated
- ≡, SPECIFICATION:
1. Current Rating: 3 AMPS
 2. Insulation Resistance: 100M Ω MIN. At 500VDC
 3. Dielectric Strength: 500V for One minute
 4. Operation Temperature: -55° C ~ $+105^{\circ}$ C.

*【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】



RECOMMEND PCB LAYOUT (T=1.6)
 PCB TOLERANCE: ± 0.05

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: DR15F叉锁
			PAR D-SUB-DR-15PCM-CB
DECIMALS:	ANGLES:		DWN
X.X \pm 0.30	X. $^{\circ}$ \pm 5 $^{\circ}$		CHKD
X.XX \pm 0.25	X.X $^{\circ}$ \pm 2 $^{\circ}$	APVD	
X.XXX \pm 0.15	X.XX $^{\circ}$ \pm 1 $^{\circ}$	CUSTOMER COPY	SCALE N:A UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A