



SPECIFICATIONS  
 Rated Current:1.5AMP  
 Contact Resistance:20mΩ Max  
 Withstand Voltage:500V AC/DC  
 Insulation Resistance:1000MΩ Min  
 Operation Temperature:-40°c to +105°c

Contact Material:Brass  
 Contact Plating:Au or Sn Over Ni  
 Insulator Material:Polyester(UL94V-0)  
 Standard: PA6T  
 Max.Processing Temp: 230°C for 30-60 seconds  
 (260°C for 5 seconds)

Dimension antitheses list				
ITEM	PA	PB	PC	L
Standard	3.90	---	2.80	8.70
Alternate				

**Ordering Information**

**XDZ 200 - \* - N - Z - \* - \*\***

- No. of Rows: 1=Single Row, 2=Dual Row
- No. of Pins: 01-40 Pin
- Type: Z=直针, W=弯针, S=立端, WS=带贴
- Length: 距离
- Contact Plating: G0:Gold Flash, G1:1u" Gold, G2:2u" Gold, G3:3u" Gold, G4:10u" Gold, G5:15u" Gold, G6:30u" Gold, S0:Gold Plast/Tin, S1:Sn

			GENREL TOLERANCE	制图 DRAWING	<b>深圳讯答科技有限公司</b> ShenzhenXundaTechnology Co.,Ltd				
			DIM TOL	审核 CHECK		产品名称 TITLE	2.00 单排 直排针 (塑高2.0)	版本 REV.	A
			X.X ±0.30	批准 APPROVAL		产品料号 PART NO.	XDZ200-1-N-Z-2.0-XX	单位 UNITS	mm
			X.XX ±0.20 X.XXX ±0.10	比例 SCALE		材料 MATERIAL		页次 SHEET	1/1
1	初版发行		Angle ±3.0°	投影 Projection					
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE							