

4

3

2


1

D

D


NOTES:

- 1.Circuit:ON/OFF
 - 2.Operation force:500±200gf
 - 3.Electrical rating:15A 125VAC
8A 250VAC
12(6)A 250V~
 - 4.Contact resistance:<30mΩ
 - 5.Insulation resistance:>1000MΩ(500VDC
between open contacts)
 - 6.Dielectric strength:>1500V 1 mintute
 - 7.Color: cover is black, body is black.








雾面黑色上盖

Panel cut out(Thickness: 3mm Max)



Circuit of Switch



5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→	9	→	RANGE		SCALE		FIT					
3	取消VDE	8	→	X	±0.4	MAT'L		***					
2	公差變更	7	→	X.X	±0.3	MATERIAL NO.		DRAWING NO.					
1	公差變更	6	→	X.XX	±0.2								
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±0.5°	ROCK TEK ELECTRICAL(SHENZHEN) CO.,LTD.		RT-S02-117-R4NBB		WIF108017			

4

3

2

1