







D±0.10
02P~10P



D±0.10
11P~30P



SEC:A-A



P/N LEGEND

<u>A1253</u>	<u>HA-XP</u>	<u>N</u>	<u>0</u>	<u>X</u>	<u>NP</u>	<u>N</u>	<u>00</u>	<u>G</u>	
①	②	③	④	⑤	⑥	⑦	⑧	⑨	⑩
① Series No.									
② Connector type: HA=Type A Housing									
③ No. of circuits									
④ N=Halogen Free									
⑤ Material: 0=Nylon 66-V0									
⑥ Color: W=White ; B=Black									
⑦ Plating code: NP=Non-plating									
⑧ Plating code: N=Non-plating									
⑨ Option code: 00=Standard									
⑩ Packing code: G=Bag									

SPECIFICATIONS

Current Rating: 1A AC,DC
Voltage Rating: 150V AC,DC
Temperature Range: -25°C ~ +85°C
Contact Resistance: 20mΩ Max.
Insulation Resistance: 500MΩ Min.
Withstanding Voltage: 500V AC/minute

Circuit No.	Dimensions				Circuit No.	Dimensions			
	A	B	C	D		A	B	C	D
02P	1.25	4.40	2.75	1.10	11P	12.50	15.65	14.00	4.70
03P	2.50	5.65	4.00	1.95	12P	13.75	16.90	15.25	4.70
04P	3.75	6.90	5.25	3.20	13P	15.00	18.15	16.50	4.70
05P	5.00	8.15	6.50	3.20	14P	16.25	19.40	17.75	4.70
06P	6.25	9.40	7.75	3.20	15P	17.50	20.65	19.00	4.70
07P	7.50	10.65	9.00	3.20	20P	23.75	26.90	25.25	4.70
08P	8.75	11.90	10.25	3.20	25P	30.00	33.15	31.50	5.70
09P	10.00	13.15	11.50	3.20	30P	36.25	39.40	37.75	5.70
10P	11.25	14.40	12.75	3.20					



燦達電子工業股份有限公司
JOINT TECH ELECTRONIC IND. CO., LTD.

UNIT SCALE SHEET
mm 1 : 1 1 of 1

DRAWN BY 朱恆秀
2009.01.05

APPROVED BY 謝瑞清
2009.01.05

GENERAL TOLERANCE
X. X±0.25
X. XX±0.15
X. XXX±0.05

TITLE:

1.25mm PITCH
HOUSING-LOCK TYPE

DRAW NO. : A1253HA-XPNXXXXXXXXX
REV. A4