

1



2

3

4

This document contains proprietary information and such information may not be disclosed to others for any purposes, not used for sales/marketing/procurement purposes without written permission

REV	DESCRIPTION OF REVISION	ECN NO.	BY	DATE	APPROVED
A	Initial Release	—	H.wei	12/7/06	12/7/06



### 1 电气性能

- 1.1 特性阻抗 50Ω
- 1.2 频率 DC~6GHz
- 1.3 介质耐压 1000V
- 1.4 中心导体电阻 < 3MΩ
- 1.5 外导体电阻 < 2MΩ
- 1.6 绝缘电阻 > 5000MΩ
- 1.7 VSWR < 1.2

### 2 材料及涂覆



- 2.1 外壳: 黄铜, 镀金
- 2.2 绝缘子: teflon
- 2.3 内导体: 锡青铜, 镀金

Tel: Lee +86-28-85589664

Web: www.hltechips.com

### Notes:

- 1. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE NOTICE AT ANY TIME
- 2. CUSTOMER OUTLINE DRAWING FOR REFERENCE ONLY

DRAWN: H.wei 12/07/06	TITLE: RF Coaxial Connector SMA Female Flange Connector Mount					
ENGINEER: L.yu 12/07/06						
APPROVED: W.yi 12/07/06		 DIMENSION IN MILLIMETERS (mm)				
TOLERANCES UNLESS OTHERWISE SPECIFIED		PART NO: HL-SMA-KFD1011	SIZE: A4	SCALE: N/A	SHEET: 1/1	REV: A
X	±0.50					
.X	±0.20					
.XX	±0.10					
ANGLES	±1°					

1

2

3

4