


HLT-2/8-2S

2-Way Power Divider


Specifications

SN	Parameters	Specifications
1	频率范围 Frequency Range	2000~8000 MHz
2	插入损耗 Insertion Loss	≤ 0.6dB (Excluding theoretical loss 未含理论损耗 3.0 dB)
3	输入驻波 Input Port VSWR	Typ.1.16 / Max.1.25
4	输出驻波 Output Port VSWR	Typ.1.14 / Max.1.20
5	隔离度 Isolation	Typ.28dB / Min.20dB
6	幅度平衡 Amplitude Balance	±0.2dB
7	相位平衡 Phase Balance	±3°
8	阻抗 Impedance	50 Ohms
9	端口接头 Input/Output Connectors	SMA-Female (Passivated Stainless Steel)
10	承受功率 Power Rating	Splitter 分路器用时 30W; Combiner 合路器用时 2W
11	工作温度 Operation Temperature	-45°C ~ +85°C
12	表面处理 Surface Finishing	Black paint 黑色烤漆
13	外形尺寸 Outline Dimensions	28*28*10 (mm)
14	重量 Weight	21 (g)




Note: Dimensions (mm / [inch]), General tolerance (±0.3)

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech




HenryTech

HenryTech



HenryTech

HenryTech



HenryTech

HenryTech



HenryTech