



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	CN INITIAL RELEASE	06/28/2023	BZHANG	WLI



MODEL NO.	JACKET COLOR	LENGTH	
		METERS	FEET
TRD855SCR-1M	GRAY	1.0	3.28
TRD855SCR-2M	GRAY	2.0	6.56
TRD855SCR-3M	GRAY	3.0	9.84
TRD855SCR-4M	GRAY	4.0	13.12
TRD855SCR-5M	GRAY	5.0	16.41
TRD855SCR-7M	GRAY	7.0	22.97
TRD855SCR-10M	GRAY	10.0	32.81
TRD855SCR-12M	GRAY	12.0	39.37
TRD855SCR-15M	GRAY	15.0	49.22
TRD855SCR-20M	GRAY	20.0	65.62
TRD855SCR-25M	GRAY	25.0	82.02
TRD855SCR-30M	GRAY	30.0	98.43

NOTES

- 1.PLUG CONFORMS TO TIA-1096
- 2.OPERATING TEMPERATURE RANGE:-10°C TO +75°C
- 3.CABLE ASSEMBLY TO BE TESTED FOR CONTINUITY
- 4.CABLE ASSEMBLY TO BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] .XX = ± .02 [.5] .XXX = ± .005 [.13] FRACTIONS ± 1/32 ANGLES ± 1° THIRD-ANGLE PROJECTION 	APPROVALS	DATE	 an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY B.ZHANG	06/21/2023	
	CHECKED BY WLI	06/21/2023	
	APPROVED BY WLI	06/21/2023	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY TELECOM/MODULAR		PRODUCT DESCRIPTION CA RJ45/RJ45 CAT5e SHILD PVC
	SIZE A	CAGE CODE 43321	
	ITEM NO. TRD855SCR-xxM	REV. A	
SCALE: NONE		CAD FILE: TRD855SCR-xxM.SLDDRW	SHEET 1 OF 1