



注： 本板为禁止转输、复制、编辑或存档，以及利用其内容进行交流



NOTES:

UL Standard

1. Use group	B	C	D
Rated Current	10A	/	10A
Rated Voltage	300V	/	300V

2. Wire range: 24~12AWG

IEC Standard

1. Pollution Degree	3	2	2
Overvoltage Category	III	III	II
Rate Impulse Voltage(KV)	/	4.0KV	/
Rate Voltage(V)	/	320V	/
Rate Current(A)	/	12A	/

2. wire range: 0.2~2.5mm²

NOTES2:

- 1.Housing: PA66 (UL94-V-0)
- 2.Cover: PA66 (UL94-V-0)
- 3.Button: POM
- 4.Conductor: Copper alloy (Ni Plated)
- 5.Spring: Stainless Steel
- 6.Screw: Steel (M2.5,Zn Plated)

NOTES3:

- 1.Pitch: 5.08mm Poles: 02-24P
- 2.Stripping length: 9-10mm
- 3.Operating temperature: -40℃~+105℃
- 4.RoHS Compliance

How to order

MX2EDGKD - 508 - XXP - XXXX - XX - X

产品型号

间距

颜色:

01:常规颜色

A-Z其他定制

灰色:GY 棕色:OE 02-99:

蓝色:BU 红色:RD 定制颜色

黑色:BK 透明色:TT

绿色:GN 黄色:YW

透明色:TT 白色:WE

Cu:铜
Fe:铁

Pitch	Range	In mm	Nominal Dimension	Range
mm		In mm		

Over 6	Over 10	Over 30	Over 60	Over 100	Over 150	0.1/10		
TO 6	TO 10	TO 30	TO 60	TO 100	TO 150	$\leq$		
± 0.15	± 0.20	± 0.30	± 0.30	± 0.50	± 0.70	± 1.00	± 1.30	$\pm 2^\circ$

REV	ECN NO.	CONTENT	CHK	DATE
-----	---------	---------	-----	------

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL		NOTE
DWG.	CHK	DATE	23.06.08	UNITS	MM	SHEET/OF 1/1
CHK		DATE		SCALE	1 : 1	A4
APP.		DATE				
CIXI MAIXU ELECTRONICS CO.,LTD				NAME	MX2EDGKD-5.08-XXP	
MAIXU 慈溪市迈旭电子有限公司				DWGNO.		