






P/N LEGEND

A2004 HA-2XNP N 0 W NP N S1 G
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩

- ① Series No.
- ② Connector type: HA=Housing A Type
- ③ No. of circuits
- ④ N=Halogen Free
- ⑤ Material: 0=Nylon 66-V0
- ⑥ Color: W=White
- ⑦ Plating code: NP=Non-plating
- ⑧ Plating code: N=Non-plating
- ⑨ Option code: S1=Special option
- ⑩ Packing code: G=Bag

SPECIFICATIONS

Current Rating: 3A AC,DC
Voltage Rating: 250V AC,DC
Temperature Range: -25°C ~ +85°C
Contact Resistance: 10mΩ Max.
Insulation Resistance: 1000MΩ Min.
Withstanding Voltage: 800V AC/minute
Material: Nylon 66,UL94V-0
Color: White

Circuit No.	Dimensions		Circuit No.	Dimensions	
	A	B		A	B
2X02P	2.00	4.50	2X12P	22.00	24.50
2X03P	4.00	6.50	2X13P	24.00	26.50
2X04P	6.00	8.50	2X14P	26.00	28.50
2X05P	8.00	10.50	2X15P	28.00	30.50
2X06P	10.00	12.50	2X16P	30.00	32.50
2X07P	12.00	14.50	2X17P	32.00	34.50
2X08P	14.00	16.50	2X18P	34.00	36.50
2X09P	16.00	18.50	2X19P	36.00	38.50
2X10P	18.00	20.50	2X20P	38.00	40.50
2X11P	20.00	22.50			



燦達電子工業股份有限公司
JOINT TECH ELECTRONIC IND. CO., LTD.

UNIT SCALE SHEET
mm 1 : 1 1 of 1

DRAWN BY 歐陽小強
2008.09.05
APPROVED BY 謝瑞清
2008.09.05

GENERAL TOLERANCE

X. X±0.25
X. XX±0.15
X. XXX±0.05

TITLE:

2.00mm PITCH
HOUSING-LOCK TYPE

DRAW NO. : A2004HA-2XNPXXXXXS1X
REV. A1