



NOTE:
1.MATERIAL:
a.HOUSING:PPA
b.CONTACT:PHOSPHOR BRONZE
(SURFACE PLATING: Au1u")
SEE ORDERING INFORMATION

2.ELECTRIC:
a.CONTACT RESISTANCE: 30 MILLIOHMS MAX
b.INSULATION RESISTANCE: 100 MEGA OHMS MIN
c.DIELECTNIC VOLTAGE: 500V AC ONE MINUTE
d.OPERATING TEMPERATURE: -25° C~ +85° C







ORDERING INFORMATION
BS-08-B2BA030-R

电池座系列
BS-08系列
SMT 180° TYPE

PLATING:
A-Au1U"
J-Ni100U"~120U"
K-Sn100U"~120U"

MATERIAL:
1A-PBT BLACK
1B-PA66 BLACK
2A-PPA BROWN
2B-PPA BLACK
3A-PPS BROWN
3B-PPS BLACK
4A-LCP WHITE
4B-LCP BLACK

工程部
2023-11-15
H. WANG




PCB Layout Diagram
Top View

3	TERMINAL(-)	1	PHOSPHOR BRONZE, T=0.20mm	Gold Plating and Ni Under-Plating
2	TERMINAL(+)	1	PHOSPHOR BRONZE, T=0.25mm	Gold Plating and Ni Under-Plating
1	HOUSING	1	PPA	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美用 www.meiyangdz.com			
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10	ANGLES: X :±1° X.X :±0.5°	DSND WangHeng	DATE 2023-11-15	TITLE: BS-2032-8CGZ2.0 5MM SMT 卷装	
WEIGHT: 9		CHKD ZhouRuicai	DATE 2023-11-15	PART NO.: BS-08-B2BA030-R	
SHEET 1 OF 2		APVD XueShunyang	DATE 2023-11-15	DRAW NO.:MY-CP-0167	
SCALE:		SIZE: A4	VIEW: ④ ①		
UNIT: mm		REV.: A/0	OBJECT: MY		



产品




圆孔

透明封带


载带

标签




标签朝上


6盘





塑料袋



外箱



Detail A



出料方向

剥离方向


余留封带长:
300 MIN

载带与封带剥离
剥离角度: 165° ~180°
剥离强度: 0.1-1.0N

10空穴
末端留空穴载带

共封装 500 只产品

15空穴
前端留空穴载带



Detail A

技术要求:

- 圆孔十个孔距离累计允许公差为 $\pm 0.2\text{mm}$
- 带长250mm内容许弯曲度1mm
- 材料厚度以在载带边缘测量为准
- 所有尺寸定义依循EIA-481-C系准则定义之
- 材料: 黑色PS T=0.35mm
- 所有卷轮为灰蓝挖空旋转塑胶卷轮
- 整模成型长度: 10.5M,
- 非指明公差范围为: $\pm 0.1\text{mm}$; 超过250mm不计算累计误差
- 型腔外形凡未标明处倒角R为0.2-0.3; 拔模斜度未标注的为 3° 以下

包装信息:

- 每卷盘装产品 500 只, 卷盘外侧贴相关标签;
- 每 6 卷盘放在一个塑料袋中;
- 每外箱装6盘, 产品总数: 3000 只;
- 外箱上下用胶纸封成“工”字;
- 电池座包材BS-2032-8C 卷装 (BS-8C-01-R)。



UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyoungdz.com			
DECIMALS:	ANGLES:	DSND	WangHeng	DATE	2023-11-15
X : ± 0.001	X : ± 0.001	CHKD	ZhouRuicai	DATE	2023-11-15
X.X : ± 0.002	X.X : ± 0.002	APVD	XueShunYong	DATE	2023-11-15
X.XX : ± 0.005	X.XX : ± 0.005	WEIGHT:	SCALE: 3:1	SIZE: A4	VIEW:
X.XXX : ± 0.010	X.XXX : ± 0.010	SHEET 2 OF 2	UNIT: mm	REV.: A/0	OBJECT: MY
				TITLE:	
				BS-2032-8CGZ2.0 5MM SMT 卷装	
				PART NO.:	
				BS-08-B2BA030-R	
				DRAW NO.:MY-BD-0036	