



技术指标:

- 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena.)
- 温度范围(Temperature range): -40° C ~ +105° C.
- 额定电压(Rated voltage): 50V, AC/DC(=效等)。
- 接触电阻(Contact resistance): ≤ 0.03Ω.
- 绝缘电阻(Insulation resistance): ≥ 500MΩ

| CKT | DIMA | DIMB | DIMC | CKT | DIMA | DIMB | DIMC |
|-----|-------|-------|-------|-----|-------|-------|-------|
| 4 | 1.50 | 2.52 | 5.54 | 33 | 16.00 | 17.02 | 20.04 |
| 5 | 2.00 | 3.02 | 6.04 | 34 | 16.50 | 17.52 | 20.54 |
| 6 | 2.50 | 3.52 | 6.54 | 35 | 17.00 | 18.02 | 21.04 |
| 7 | 3.00 | 4.02 | 7.04 | 36 | 17.50 | 18.52 | 21.54 |
| 8 | 3.50 | 4.52 | 7.54 | 37 | 18.00 | 19.02 | 22.04 |
| 9 | 4.00 | 5.02 | 8.04 | 38 | 18.50 | 19.52 | 22.54 |
| 10 | 4.50 | 5.52 | 8.54 | 39 | 19.00 | 20.02 | 23.04 |
| 11 | 5.00 | 6.02 | 9.04 | 40 | 19.50 | 20.52 | 23.54 |
| 12 | 5.50 | 6.52 | 9.54 | 41 | 20.00 | 21.02 | 24.04 |
| 13 | 6.00 | 7.02 | 10.04 | 42 | 20.50 | 21.52 | 24.54 |
| 14 | 6.50 | 7.52 | 10.54 | 43 | 21.00 | 22.02 | 25.04 |
| 15 | 7.00 | 8.02 | 11.04 | 44 | 21.50 | 22.52 | 25.54 |
| 16 | 7.50 | 8.52 | 11.54 | 45 | 22.00 | 23.02 | 26.04 |
| 17 | 8.00 | 9.02 | 12.04 | 46 | 22.50 | 23.52 | 26.54 |
| 18 | 8.50 | 9.52 | 12.54 | 47 | 23.00 | 24.02 | 27.04 |
| 19 | 9.00 | 10.02 | 13.04 | 48 | 23.50 | 24.52 | 27.54 |
| 20 | 9.50 | 10.52 | 13.54 | 49 | 24.00 | 25.02 | 28.04 |
| 21 | 10.00 | 11.02 | 14.04 | 50 | 24.50 | 25.52 | 28.54 |
| 22 | 10.50 | 11.52 | 14.54 | 51 | 25.00 | 26.02 | 29.04 |
| 23 | 11.00 | 12.02 | 15.04 | 52 | 25.50 | 26.52 | 29.54 |
| 24 | 11.50 | 12.52 | 15.54 | 53 | 26.00 | 27.02 | 30.04 |
| 25 | 12.00 | 13.02 | 16.04 | 54 | 26.50 | 27.52 | 30.54 |
| 26 | 12.50 | 13.52 | 16.54 | 55 | 27.00 | 28.02 | 31.04 |
| 27 | 13.00 | 14.02 | 17.04 | 56 | 27.50 | 28.52 | 31.54 |
| 28 | 13.50 | 14.52 | 17.54 | 57 | 28.00 | 29.02 | 32.04 |
| 29 | 14.00 | 15.02 | 18.04 | 58 | 28.50 | 29.52 | 32.54 |
| 30 | 14.50 | 15.52 | 18.54 | 59 | 29.00 | 30.02 | 33.04 |
| 31 | 15.00 | 16.02 | 19.04 | 60 | 29.50 | 30.52 | 33.54 |
| 32 | 15.50 | 16.52 | 19.54 | 80 | 39.50 | 40.52 | 43.54 |

 兆星精密电子(深圳)有限公司

RoHS

一般公差(TOLERANCE)
 $X \pm 0.50$ $XX \pm 1.0$
 $X \pm 0.20$ $XXX \pm 0.5$
 ANGLES $\pm 1^\circ$

| 品名(TITLE) | 制图(DR) |
|---------------------|-----------|
| 0.5间距 2.0高度 后翻盖式 镀金 | |
| 料号(DWG.NO.) | 校对(CHKD) |
| ZX-0.5FPC-2H-HJF22P | |
| 比例(SCALE) | 审核(APPD) |
| 1:1 | |
| 单位(UNITS) | 张数(SHEET) |
| mm | 1 OF 1 |
| SIZE | REV |
| A4 | A |