


SPECIFICATIONS

- Current Rating: 3Amps
- Insulation Resistance: 1000MΩ Min
- Contact Resistance: 20MΩ Max
- Withstanding Voltage: AC 1000V
- Operation Temperature: -40° to +105°
- Contact Material: Brass
- Standard: PBT
- Insulator Material: Polyester (UL 94V-0)
- Contact Plating: Gold Flash
- Max. Processing Temp: 200° C for 30-60 seconds (220° C for 5 seconds)



UNLESS OTHERWISE SPECIFIED TOLERANCE		DRAWN NAME: 2.54DC2-NP in H17 180度 PC3.8 PBT									
X	: ±0.30	X°	: ±5°	SIZE	A4	SCALE	N: 1	PROUCT NO.	ZX-IDC2.54-2-8PZN		
X.X	: ±0.25	X.X°	: ±1°	REV	A	UNIT	mm	PROJECT	PAGE 1/1		
X.XX	: ±0.20	X.XX°	: ±0.5°	CHECKED:	CHECKED:			/ /	APPROVED:	/ /	