



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

SPECIFICATIONS

- Current Rating: 3Amps
- Insulation Resistance: 1000MΩ Min
- Contact Resistance: 20MΩ Max
- Withstanding Voltage: AC 1000V
- Operation Temperature: -40° to +105°
- Contact Material: Brass
- Standard: PBT
- Insulator Material: Polyester (UL 94V-0)
- Contact Plating: Gold Flash
- Max. Processing Temp: 200° C for 30-60 seconds
(220° C for 5 seconds)



兆星精密电子 (深圳) 有限公司

UNLESS OTHERWISE SPECIFIED TOLERANCE		DRAWN NAME: 2.54DC2-NP in H17 180度 PC3.8 PBT								
X	: ±0.30	X°	: ±5°	SIZE	A4	SCALE	N: 1	PROUCT NO.	ZX-1DC2.54-2-20PZN	
X.X	: ±0.25	X.X°	: ±1°	REV	A	UNIT	mm	PROJECT		PAGE 1/1
X.XX	: ±0.20	X.XX°	: ±0.5°	CHECKED:	CHECKED:	/ /	APPROVED:	/ /		