




A4				 台普 ROCPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91934G124RA
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw
A1					X.X	± 0.15	ROCPU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE	X	± 0.25					
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission				

A		B		C		D		E		F		G		
1	性能参数													
	1. Heating current: Ui: AC250V, Ith: 5A 发热电流: Ui: AC250V, Ith: 5A						13. Electrical life: 500000 cycles 电气寿命: 500000 cycles							
	2. Rated current:3A/DC36V 额定电流:3A/DC36V						14. mechanical: 500000cycles 机械寿命: 500000cycles							
	3. Power-frequency withstand voltage:1500V1min 工频耐压:1500V1min						15. Operation method:Self-locking 操作方式: 自锁式							
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ						16. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N							
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ						17. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下							
	6. Pressing stroke:2.80mm ± 0.10 按压行程:2.80mm ± 0.10						18. LED lamp lifespan: 40000h LED寿命: 40000h							
	7. Contact stroke:1.00mm±0.10 接触行程 :1.00mm±0.10						19. LED color: Red LED颜色: 红色							
	8. Nut assembly torque:5-14N 螺帽装配力矩:5-14N													
	9. Protection level:IP67 防护等级:IP67													
2	10. Explosion prevention level: IK10 防暴等级: IK10													
	11. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃													
	12. Compression torque: ≤ 4N 按压扭力: ≤4N													
	连接形式													
	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下													
	2. Can be used with dedicated connectors: 可配专用接插件使用:													
	2.1 Switch function wire: blue wire (NO) 开关功能线材: 蓝线 (NO)													
	2.2 LED functional wire: red wire positive pole, black wire negative pole, LED without distinction between positive and negative poles LED功能线材: 红线正极, 黑线负极, LED不分正负极													
5	A4				 台普 ROC PU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:		
	A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91934G124RA		
	A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw				
	A1					ROC PU TECHNOLOGY CO.,LTD								
	REV	DATE	REVISION	DESCRIPTION										ISSUE
	A		B			C		D		E		F		G

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission.

A		B		C		D		E		F		G	
材质参数													
10	luminous zone 发光区			PC 塑料		1							
9	LEDpin LED脚			Brass 黄铜		1		Silvering 镀银					
8	Base 底座			PA46		1							
7	Pin 引脚			Brass 黄铜		1		gold-plating 镀金					
6	Contact material 接触材质			silver alloy 银合金		1		Silvering 镀银					
5	Base 基座			PA66		1							
4	Arm nut 固定螺帽			Brass 黄铜		1		nickeling 镀镍					
3	Oring O型圈			Silica gel 硅胶		1							
2	Housing 外壳			Aluminum alloy 铝合金		1		Oxidized/Black 氧化/黑色					
1	Key 按键			Aluminum alloy 铝合金		1		Oxidized/Black 氧化/黑色					
NO 序号	Part name 部件名			Material 材料		QTY 数量		Remark 备注					

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:		
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91934G124RA		
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw				
A1					ROCPCU TECHNOLOGY CO.,LTD								
REV	DATE	REVISION	DESCRIPTION										ISSUE
					ANGULAR		—		Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				
A		B		C		D		E		F		G	