





[illegible]

A					B					C					D					E					F					G				
材质参数																																		
10					luminous zone 发光区					PC 塑胶					1																			
9					LEDpin LED引脚					Brass 黄铜					1					Silvering 镀银														
8					Base 底座					PA46					1																			
7					Pin 引脚					Brass 黄铜					1					gold-plating 镀金														
6					Contact material 接触材质					silver alloy 银合金					1					Silvering 镀银														
5					LED Base LED基座					PC 塑胶					1																			
4					Arm nut 固定螺帽					Brass 黄铜					1					nickeling 镀镍														
3					Oring O型圈					Silica gel 硅胶					1																			
2					Housing 外壳					Aluminum alloy 铝合金					1					Oxidized/Black 氧化/黑色														
1					Key 按键					Aluminum alloy 铝合金					1					Oxidized/Black 氧化/黑色														
NO 序号					Part name 部件名					Material 材料					QTY 数量					Remark 备注														


A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP93009P224RA5150
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR					



A4					 台普 ROC CPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3								DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP93009P224RA5150
A2						X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1						X.X	± 0.15	ROC CPU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE		X	± 0.25					
						ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				

	A		B		C		D		E		F		G
1	性能参数 1.L1-导线长度：默认150MM长； 2.L2-线头长度：默认10MM 3.L3-剥头长度：默认3MM 4.S-导线导体横截面积：默认0.5平方MM、可选0.3平方MM 5.线型拉力N：（0.15-0.25MM）≤30N、（0.3MM）≤40N、（0.5MM）≤50N、（0.75MM）≤60N 6.需要其他线长、线型、可以定制												
2	材质参数 1.插壳：浅蓝色尼龙胶壳 2.端子：磷铜y镀锡色 3.导电线材：紫铜												
3	线束使用说明 1.2线：用于单色的指示灯、无开关功能 2.3线：用于双色指示灯、无开关功能 3.4线：用于三色灯的指示灯、无开关功能 4.3线：用于1N0/1N01NC开关、无指示灯功能 5.6线：用于2N0/2N02NC开关、无指示灯功能 6.5线：用于1N0/1N01NC、单色指示灯带开关功能 7.8线：用于2N0/2N02NC、单色指示灯带开关功能 8.6线：用于1N0/1N01NC、双色指示灯带开关功能 9.7线：用于1N0/1N01NC、三色或220v双色指示灯带开关功能												
4													
5	A4				台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJCTED		PRODUCT NAME:	
A3				DRAWN BY				FUYUAN	CHECKED BY	COCO	MODEL NO:TP93009P224RA5150		
A2						X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw	
A1						X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD					
REV	DATE	REVISION	DESCRIPTION	ISSUE		X	± 0.25						
						ANGULAR	——	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission					
	A		B		C		D		E		F		G

30MM系列单排单色按钮开关接线说明



接线说明:

- 1、供电电源的负极、设备的负极、按钮开关的LED负极，并接一起。
- 2、供电电源的正极，按钮开关的C脚，并接一起。
- 3、设备的正极，按钮开关的NO脚、按钮开关的LED正极，并接一起。

实现功能:

- 1、按钮开关按下去时：设备通电，按钮开关LED灯亮。
- 2、按钮开关按回去时：设备断电，按钮开关LED灯灭。

注：说明图的电压为接线参考使用，电源电压根据实际供电电压为准。

红线为正极 (火线)
黑线为负极 (零线)

A4				 ROC CPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:					
A3								DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO:				
A2						X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw				
A1						X.X	± 0.15	ROC CPU TECHNOLOGY CO.,LTD								
						X	± 0.25									
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR	_____	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission								
				A		B		C		D		E		F		G