




A		B		C		D		E		F		G	
1	性能参数												
	1. Heating current: Ui: AC250V, Ith: 5A 发热电流: Ui: AC250V, Ith: 5A						13. Electrical life: 500000 cycles 电气寿命: 500000 cycles						
	2. Rated current:3A/DC36V 额定电流:3A/DC36V						14. mechanical: 500000cycles 机械寿命: 500000cycles						
	3. Power-frequency withstand voltage:1500V1min 工频耐压:1500V1min						15. Operation method:Self-locking 操作方式: 自锁式						
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ						16. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N						
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ						17. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下						
	6. Pressing stroke:2.80mm ± 0.10 按压行程:2.80mm ± 0.10						18. LED lamp lifespan: 40000h LED寿命: 40000h						
	7. Contact stroke:1.00mm±0.10 接触行程 :1.00mm±0.10						19. LED color: Red LED颜色: 红色						
	8. Nut assembly torque:5-14N 螺帽装配力矩:5-14N												
	9. Protection level:IP67 防护等级:IP67												
2	10. Explosion prevention level: IK10 防暴等级: IK10												
	11. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃												
	12. Compression torque: ≤ 4N 按压扭力: ≤4N												
	连接形式												
	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下												
	2. Can be used with dedicated connectors: 可配专用接插件使用:												
	2.1 Switch function wire: blue wire (NO) 开关功能线材: 蓝线 (NO)												
	2.2 LED functional wire: red wire positive pole, black wire negative pole, LED without distinction between positive and negative poles LED功能线材: 红线正极, 黑线负极, LED不分正负极												
3													
4													
5													



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT

MM

PROJECTED



PRODUCT NAME:

DRAWN BY

FUYUAN

CHECKED BY

COCO

MODEL NO: TP91932G124RA5150B

DATE

2019

APPROVAL B

ALEN


Https: www.rocpcu.tw

ROC PCU TECHNOLOGY CO., LTD

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission

A					B					C					D					E					F					G				
1	材质参数																																	
	10					luminous zone 发光区					PC 塑料					1																		
	9					LEDpin LED脚					Brass 黄铜					1					Silvering 镀银													
	8					Base 底座					PA46					1																		
	7					Pin 引脚					Brass 黄铜					1					gold-plating 镀金													
	6					Contact material 接触材质					silver alloy 银合金					1					Silvering 镀银													
	5					Base 基座					PA66					1																		
	4					Arm nut 固定螺帽					Brass 黄铜					1					nickeling 镀镍													
	3					Oring O型圈					Silica gel 硅胶					1																		
	2					Housing 外壳					Aluminum alloy 铝合金					1					Oxidized/Black 氧化/黑色													
4	1					Key 按键					Aluminum alloy 铝合金					1					Oxidized/Black 氧化/黑色													
	NO 序号					Part name 部件名					Material 材料					QTY 数量					Remark 备注													


A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:																							
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91932G124RA5150B																							
A2							DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw																							
A1							ROCPCU TECHNOLOGY CO.,LTD																											
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission																											
A					B					C					D					E					F					G				



A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91932G124RA5150B
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE	X	± 0.25					
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				

	A	B	C	D	E	F	G																														
1	性能参数 1.L1-导线长度：默认150MM长； 2.L2-线头长度：默认10MM 3.L3-剥头长度：默认3MM 4.S-导线导体横截面积：默认0.5平方MM、可选0.3平方MM 5.线型拉力N：（0.15-0.25MM²）≤30N、（0.3MM²）≤40N、（0.5MM²）≤50N、（0.75MM²）≤60N 6.需要其他线长、线型、可以定							1																													
2	材质参数 1.插壳：浅蓝色尼龙胶壳 2.端子：磷铜y镀锡色 3.导电线材：紫铜							2																													
3	线束使用说明 1.2线：用于单色指示灯、无开关功能 2.2线：用于1NO开关、无指示灯功能 3.4线：用于1NO开关、单色指示灯带灯开关功能							3																													
4								4																													
5	A4				 台普 ROCPCU		<table border="1"> <tr> <td>COMMON TOLERANCE</td> <td>UNIT</td> <td>MM</td> <td>PROJCTED</td> <td rowspan="4">  </td> <td>PRODUCT NAME:</td> </tr> <tr> <td>X.XX ± 0.10</td> <td>DRAWN BY</td> <td>FUYUAN</td> <td>CHECKED BY</td> <td>COCO</td> <td>MODEL NO: TP91932G124RA5150B</td> </tr> <tr> <td>X.X ± 0.15</td> <td>DATE</td> <td>2019</td> <td>APPROVAL B</td> <td>ALEN</td> <td>Https: www.rocpcu.tw</td> </tr> <tr> <td>X ± 0.25</td> <td colspan="4"> ROCPCU TECHNOLOGY CO.,LTD Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission </td> </tr> <tr> <td>ANGULAR</td> <td colspan="5"></td> </tr> </table>	COMMON TOLERANCE	UNIT	MM	PROJCTED		PRODUCT NAME:	X.XX ± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91932G124RA5150B	X.X ± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw	X ± 0.25	ROCPCU TECHNOLOGY CO.,LTD Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission				ANGULAR						5
COMMON TOLERANCE	UNIT	MM	PROJCTED		PRODUCT NAME:																																
X.XX ± 0.10	DRAWN BY	FUYUAN	CHECKED BY		COCO	MODEL NO: TP91932G124RA5150B																															
X.X ± 0.15	DATE	2019	APPROVAL B		ALEN	Https: www.rocpcu.tw																															
X ± 0.25	ROCPCU TECHNOLOGY CO.,LTD Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission																																				
ANGULAR																																					
	REV	DATE	REVISION	DESCRIPTION	ISSUE																																
	A	B	C	D	E	F	G																														

19MM系列单色按钮开关接线说明



接线说明:

- 1、供电电源的负极、设备的负极、按钮开关的LED负极，并接一起。
- 2、供电电源的正极，按钮开关的一只NO脚，并接一起。
- 3、设备的正极，按钮开关的另外一只NO脚、按钮开关的LED正极，并接一起。

实现功能:

- 1、按钮开关**按下去**时: 设备**通电**, 按钮开关LED**灯亮**。
- 2、按钮开关**按回去**时: 设备**断电**, 按钮开关LED**灯灭**。

注: 说明图的电压为接线参考使用, 电源电压根据实际供电电压为准。

红线为正极 (火线)
黑线为负极 (零线)

A4					 台普 ROC CPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3								DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO:
A2						X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1						X.X	± 0.15	ROC CPU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE		X	± 0.25					
						ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission				