




5	A4				 台普 ROC CPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:		
	A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91642G124RA		
	A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw		
	A1					X.X	± 0.15	ROC CPU TECHNOLOGY CO.,LTD						
	REV	DATE	REVISION	DESCRIPTION		ISSUE	X							± 0.25
						ANGULAR	——	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission						
		A		B		C		D		E		F		G

	A	B	C	D	E	F	G				
1	性能参数				13. mechanical: 500000cycles 机械寿命: 500000cycles						
	1. Heating current: Ui: AC250V, Ith: 3A 发热电流: Ui: AC250V, Ith: 3A				14. Operation method:Self-locking 操作方式: 自锁式						
	2. Rated current:2A/DC36V 额定电流:2A/DC36V				15. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N						
	3. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ				16. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下						
	4. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ				17. LED lamp lifespan: 40000h LED寿命: 40000h						
	5. Pressing stroke:2.80mm ± 0.10 按压行程:2.80mm ± 0.10				18. LED color: Red LED颜色: 红色						
2	6. Contact stroke:1.10mm±0.10 接触行程 :1.10mm±0.10										
	7. Nut assembly torque:5-14N 螺帽装配力矩:5-14N										
	8. Protection level:IP67 防护等级:IP67										
	9. Explosion prevention level: IK09 防暴等级: IK09										
	10. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃										
	11. Compression torque: ≤ 3N 按压扭力: ≤3N										
3	12. Electrical life: 500000 cycles 电气寿命: 500000 cycles										
4											
5	A4			台普 ROCPCU	COMMON TOLERANCE	UNIT	MM	PROJECTED		PRODUCT NAME:	
	A3					DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91642G124RA	
	A2				X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
	A1				X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD				
	REV	DATE	REVISION DESCRIPTION	ISSUE	X	± 0.25					
					ANGULAR	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission					
	A	B	C	D	E	F	G				

	A	B	C	D	E	F	G	
1	材质参数						1	
	9	luminous zone 发光区	PC 塑料	1				
2	8	LEDpin LED脚	Brass 黄铜	1	Silvering 镀银			
	7	Pin 引脚	Brass 黄铜	1	gold-plating 镀金			
	6	Contact material 接触材质	Silvering 镀银	1				
3	5	Base 基座	PA66	1	Black 黑色			
	4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍			
	3	Oring O型圈	Silica gel 硅胶	1				
4	2	Housing 外壳	Aluminum alloy 铝合金	1	Oxidized/Black 氧化/黑色			
	1	Key 按键	Aluminum alloy 铝合金	1	Oxidized/Black 氧化/黑色			
	NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注			
5	A4							
	A3							
	A2							
	A1							
	REV	DATE	REVISION DESCRIPTION	ISSUE	 COMMON TOLERANCE X.XX ± 0.10 X.X ± 0.15 X ± 0.25 ANGULAR UNIT DRAWN BY FUYUAN DATE MM 2019 PROJECTED CHECKED BY APPROVAL B  COCO ALEN PRODUCT NAME: MODEL NO: TP91642G124RA Https: www.rocpcu.tw			
ROCPCU TECHNOLOGY CO.,LTD Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission								
	A	B	C	D	E	F	G	