



NOTES:
 1.CAGE; COPPER ALLOY THICKNESS:0.25mm;
 2.CLIP; STAINLESS STEEL
 3.LIGHT PIPE; POLYCARBONATE COLOR CLEAR

BEZEL
 RECOMMENDED PANEL CUTOUT AND PC BOARD
 PANEL POSITION AND THICKNESS 0.8-2.6

BEZEL OPENING
 BELOW TOP OF PCB
 PCB THICKNESS

BEZEL
 RECOMMENDED PANEL CUTOUT AND PC BOARD
 PANEL POSITION AND THICKNESS 0.8-2.6

BEZEL OPENING
 BELOW TOP OF PCB
 PCB THICKNESS

RECOMMENDED PCB LAYOUT (COMPONENT SIDE)

RECOMMENDED MINIMUM PCB THICKNESS:1.50mm
 (ALL TOLERANCES ARE ±0.05)

RECOMMENDED PCB CONFIGURATION WITH KEEP-OUT
 AREAS SINGLE SIDED APPLICATIONS

RECOMMENDED PCB LAYOUT (COMPONENT SIDE)

RECOMMENDED MINIMUM PCB THICKNESS:2.25mm
 (ALL TOLERANCES ARE ±0.05)

RECOMMENDED PCB CONFIGURATION WITH
 KEEP-OUT AREAS BELLY TO BELLY APPLICATIONS

		GENREL TOLERANCE	制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
		DIM TOL	审核 CHECK	产品名称 TITLE	SPF 外壳 (压接式 带导光柱)	版本 REV.	A
		X.X ±0.30	批准 APPROVAL	产品料号 PART NO.	HC-SFP-1x4-05L-WLP-03	单位 UNITS	mm
1	初版发行	X.XX ±0.20	比例 SCALE	材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	投影 Projection				