




A4				 台普 ROC CPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP991605G124RS
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X	± 0.15	ROC CPU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE	X	± 0.25					
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission				

	A	B	C	D	E	F	G				
1	性能参数										
	1. Heating current: Ui: AC250V, Ith: 10A 发热电流: Ui: AC250V, Ith: 10A				12. Compression torque: ≤ 5.0N 按压扭力: ≤5.0N						
	2. Rated current:10A,AC110V/220V 10A,DC12V/24V 额定电流:10A,AC110V220V 10A,DC12V/24V				13. Electrical life: 50,000 cycles 电气寿命: 50,000 cycles						
	3. Power-frequency withstand voltage:1500V/1min 工频耐压:1500V/1min				14. Mechanical: 500,000cycles 机械寿命: 500,000cycles						
2	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ				15. Operation method:self-locking 操作方式: 自锁式						
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ				16. LED lamp power consumption: 20mA以下 LED灯功耗: 20mA以下						
	6. Pressing stroke:4.00mm ± 0.10 按压行程:4.00mm ± 0.10				17. LED lamp lifespan: 40000h LED寿命: 40000h						
	7. Contact stroke:1.20mm±0.10 接触行程 :1.20mm±0.10				18. LED color: Red LED颜色: 红色						
	8. Nut assembly torque:5-14N.m 螺帽装配力矩:5-14N.m				19. LED Lamp Voltage: 24V LED灯电压: 24V						
	9. Protection level:IP67 防护等级:IP67				20. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N						
	10. Explosion prevention level: IK10 防暴等级: IK10										
3	11. Working environment temperature: -40 ℃~+80 ℃ 工作环境温度: -40 ℃~+80 ℃										
	连接形式										
	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下										
4	2. Can be used with dedicated connectors: 可配专用接插件使用:										
	2.1 Switch function wire: Blue wire (NO) (1.0²mm) 开关功能线材: 蓝线 (NO) (1.0²mm)										
	2.2 LED functional wire: red wire positive pole black wire negative pole(0.5²mm) LED功能线材: 红线正极 黑线负极 (0.5²mm)										
	2.3 LED is an electrodeless lamp bead that can be lit without the need to separate positive and negative poles LED为无极灯珠, 无需分正负极也可点亮										
	A4			 台普 ROC PU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
5	A3						DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO:TP991605G124RS
	A2				X.XX ± 0.10		DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
	A1				X.X ± 0.15		ROC PU TECHNOLOGY CO.,LTD				
	REV	DATE	REVISION DESCRIPTION		ISSUE	X ± 0.25					
					ANGULAR	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission					
	A	B	C	D	E	F	G				

		A			B			C			D			E			F			G			
材质参数																							
1		9		luminous zone 发光区				PC 塑胶				1											
		8		LEDpin LED引脚				Brass 黄铜				1				Silvering 镀银							
2		7		Base 底座				PBT				1											
		6		NOPin NO引脚				Brass 黄铜				1				gold-plating 镀金							
		5		Contact material 接触材质				silver alloy 银合金				1				Silvering 镀银							
3		4		Arm nut 固定螺帽				Brass 黄铜				1				nickeling 镀镍							
		3		Oring O型圈				Silica gel 硅胶				1											
		2		Housing 外壳				SUS 不锈钢				1											
4		1		Key 按键				SUS 不锈钢				1											
		NO 序号		Part name 部件名				Material 材料				QTY 数量				Remark 备注							
A4								 台普 ROC CPU		COMMON TOLERANCE		UNIT		MM		PROJECTED				PRODUCT NAME:			
A3												DRAWN BY		FUYUAN		CHECKED BY		COCO		MODEL NO: TP991605G124RS			
A2										X.XX		± 0.10		DATE		2019		APPROVAL B		ALEN		Https: www.rocpcu.tw	
A1										X.X		± 0.15		ROC CPU TECHNOLOGY CO.,LTD									
REV		DATE		REVISION DESCRIPTION		ISSUE				X		± 0.25											
								ANGULAR		——		Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission											
		A				B				C				D				E				F	