




A4				 台普 ROC CPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91934G124RAB
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X	± 0.15	ROC CPU TECHNOLOGY CO., LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE	X	± 0.25					
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission				

A	B	C	D	E	F	G																																																																									
性能参数 1. Heating current: Ui: AC250V, Ith: 5A 发热电流: Ui: AC250V, Ith: 5A 2. Rated current:3A/DC36V 额定电流:3A/DC36V 3. Power-frequency withstand voltage:1500V1min 工频耐压:1500V1min 4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ 5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ 6. Pressing stroke:2.80mm ± 0.10 按压行程:2.80mm ± 0.10 7. Contact stroke:1.00mm±0.10 接触行程 :1.00mm±0.10 8. Nut assembly torque:5-14N 螺帽装配力矩:5-14N 9. Protection level:IP67 防护等级:IP67 10. Explosion prevention level: IK10 防暴等级: IK10 11. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃ 12. Compression torque: ≤ 4N 按压扭力: ≤4N 13. Electrical life: 500000 cycles 电气寿命: 500000 cycles 14. mechanical: 500000cycles 机械寿命: 500000cycles 15. Operation method:Self-locking 操作方式: 自锁式 16. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N 17. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下 18. LED lamp lifespan: 40000h LED寿命: 40000h 19. LED color: Red LED颜色: 红色 连接形式 1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下 2. Can be used with dedicated connectors: 可配专用接插件使用: 2.1 Switch function wire: blue wire (NO) 开关功能线材: 蓝线 (NO) 2.2 LED functional wire: red wire positive pole, black wire negative pole, LED without distinction between positive and negative poles LED功能线材: 红线正极, 黑线负极, LED不分正负极 <table><tr><td>A4</td><td></td><td></td><td></td><td rowspan="5"> 台普 ROC PU</td><td colspan="2" rowspan="2">COMMON TOLERANCE</td><td>UNIT</td><td>MM</td><td>PROJECTED</td><td></td><td>PRODUCT NAME:</td></tr><tr><td>A3</td><td></td><td></td><td></td><td>DRAWN BY</td><td>FUYUAN</td><td>CHECKED BY</td><td>COCO</td><td>MODEL NO: TP91934G124RAB</td></tr><tr><td>A2</td><td></td><td></td><td></td><td>DATE</td><td>2019</td><td>APPROVAL B</td><td>ALEN</td><td>Https: www.rocpu.tw</td></tr><tr><td>A1</td><td></td><td></td><td></td><td colspan="6" rowspan="2">ROC PU TECHNOLOGY CO.,LTD</td></tr><tr><td>REV</td><td>DATE</td><td>REVISION</td><td>DESCRIPTION</td><td>ISSUE</td><td colspan="2">ANGULAR</td><td colspan="2"></td></tr><tr><td colspan="12">Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission</td></tr><tr><td>A</td><td></td><td>B</td><td></td><td>C</td><td></td><td>D</td><td></td><td>E</td><td></td><td>F</td><td>G</td></tr></table>							A4				 台普 ROC PU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:	A3				DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91934G124RAB	A2				DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw	A1				ROC PU TECHNOLOGY CO.,LTD						REV	DATE	REVISION	DESCRIPTION	ISSUE	ANGULAR				Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission												A		B		C		D		E		F	G
A4				 台普 ROC PU	COMMON TOLERANCE		UNIT	MM	PROJECTED					PRODUCT NAME:																																																																	
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO		MODEL NO: TP91934G124RAB																																																																			
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw																																																																						
A1					ROC PU TECHNOLOGY CO.,LTD																																																																										
REV	DATE	REVISION	DESCRIPTION								ISSUE	ANGULAR																																																																			
Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission																																																																															
A		B		C		D		E		F	G																																																																				

A					B					C					D					E					F					G				
材质参数																																		
10					luminous zone 发光区					PC 塑料					1																			
9					LEDpin LED脚					Brass 黄铜					1					Silvering 镀银														
8					Base 底座					PA46					1																			
7					Pin 引脚					Brass 黄铜					1					gold-plating 镀金														
6					Contact material 接触材质					silver alloy 银合金					1					Silvering 镀银														
5					Base 基座					PA66					1																			
4					Arm nut 固定螺帽					Brass 黄铜					1					nickeling 镀镍														
3					Oring O型圈					Silica gel 硅胶					1																			
2					Housing 外壳					Aluminum alloy 铝合金					1					Oxidized/Black 氧化/黑色														
1					Key 按键					Aluminum alloy 铝合金					1					Oxidized/Black 氧化/黑色														
NO 序号					Part name 部件名					Material 材料					QTY 数量					Remark 备注														

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT		MM	PROJECTED		PRODUCT NAME:																						
A3							DRAWN BY		FUYUAN	CHECKED BY	COCO	MODEL NO: TP91934G124RAB																						
A2					X.XX	± 0.10	DATE		2019	APPROVAL B	ALEN	Https: www.rocpcu.tw																						
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD																											
REV	DATE	REVISION	DESCRIPTION		ISSUE	X							± 0.25																					
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission																											
A					B					C					D					E					F					G				