




A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJCTED		PRODUCT NAME:				
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91933P224RAB				
A2						X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw			
A1						X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD							
						X	± 0.25								
REV	DATE	REVISION	DESCRIPTION	ISSUE		ANGULAR			Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission						
		A			B		C		D		E		F		G

A	B	C	D	E	F	G								
1 1 材质参数														
9	luminous zone 发光区	PC 塑料	1											
8	LEDpin LED脚	Brass 黄铜	1		Silvering 镀银									
7	Pin 引脚	Brass 黄铜	1		gold-plating 镀金									
6	Contact material 接触材质	silver alloy 银合金	1		Silvering 镀银									
5	Base 基座	PA66	1											
4	Arm nut 固定螺帽	Brass 黄铜	1		nickeling 镀镍									
3	Oring O型圈	Silica gel 硅胶	1											
2	Housing 外壳	Aluminum alloy 铝合金	1		Oxidized/Black 氧化/黑色									
1	Key 按键	Aluminum alloy 铝合金	1		Oxidized/Black 氧化/黑色									
NO 序号	Part name 部件名	Material 材料	QTY 数量		Remark 备注									
4 4														
A4				UNIT	MM	PROJECTED								
A3				DRAWN BY	FUYUAN	CHECKED BY								
A2				DATE	2019	APPROVAL B								
A1														
REV	DATE	REVISION	DESCRIPTION	ISSUE										
5 5  台普 ROCPCU				COMMON TOLERANCE <table border="1"> <tr> <td>X.XX</td><td>± 0.10</td></tr> <tr> <td>X.X</td><td>± 0.15</td></tr> <tr> <td>X</td><td>± 0.25</td></tr> <tr> <td>ANGULAR</td><td>—</td></tr> </table>			X.XX	± 0.10	X.X	± 0.15	X	± 0.25	ANGULAR	—
X.XX	± 0.10													
X.X	± 0.15													
X	± 0.25													
ANGULAR	—													
				UNIT	MM	PROJECTED								
				DRAWN BY	FUYUAN	CHECKED BY								
				DATE	2019	APPROVAL B								
				PRODUCT NAME: MODEL NO: TP91933P224RAB Https: www.rocpcu.tw										
				ROCPU TECHNOLOGY CO.,LTD										
Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission														
A	B	C	D	E	F	G								