




A4				 ROC CPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:	
A3								DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91645P224RA
A2						X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw
A1						X.X	± 0.15	ROC CPU TECHNOLOGY CO.,LTD				
						X	± 0.25					
REV	DATE	REVISION	DESCRIPTION		ISSUE		ANGULAR	——	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission			

	A		B		C		D		E		F		G
1	性能参数 1. Heating current: Ui: AC250V, lth: 3A 发热电流: Ui: AC250V, lth: 3A 2. Rated current:2A/DC36V 额定电流:2A/DC36V 3. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ 4. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ 5. Pressing stroke:2.80mm ± 0.10 按压行程:2.80mm ± 0.10 6. Contact stroke:1.10mm±0.10 接触行程 :1.10mm±0.10 7. Nut assembly torque:5-14N 螺帽装配力矩:5-14N 8. Protection level:IP67 防护等级:IP67 9. Explosion prevention level: IK09 防暴等级: IK09 10. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃ 11. Compression torque: ≤ 3N 按压扭力: ≤3N 12. Electrical life: 500000 cycles 电气寿命: 500000 cycles 13. mechanical: 500000cycles 机械寿命: 500000cycles 14. Operation method:Self repeating form 操作方式: 自复式 15. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N 16. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下 17. LED lamp lifespan: 40000h LED寿命: 40000h 18. LED color: Red LED颜色: 红色												
2													
3													
4													
5	A4				台普 ROCPU		COMMON TOLERANCE		UNIT	MM	PROJCTED		PRODUCT NAME:
	A3								DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91645P224RA
	A2						X.XX ± 0.10		DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw
	A1						X.X ± 0.15		ROCPU TECHNOLOGY CO.,LTD				
	REV	DATE	REVISION	DESCRIPTION	ISSUE	X ± 0.25							
						ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission					
	A		B		C		D		E		F		G

A					B					C					D					E					F					G				
材质参数																																		
9					luminous zone 发光区					PC 塑料					1																			
8					LEDpin LED脚					Brass 黄铜					1					Silvering 镀银														
7					Pin 引脚					Brass 黄铜					1					gold-plating 镀金														
6					Contact material 接触材质					Silvering 镀银					1																			
5					Base 基座					PA66					1					Black 黑色														
4					Arm nut 固定螺帽					Brass 黄铜					1					nickeling 镀镍														
3					Oring O型圈					Silica gel 硅胶					1																			
2					Housing 外壳					Aluminum alloy 铝合金					1					Oxidized/Black 氧化/黑色														
1					Key 按键					Aluminum alloy 铝合金					1					Oxidized/Black 氧化/黑色														
NO 序号					Part name 部件名					Material 材料					QTY 数量					Remark 备注														

A4				 台普 ROC PU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91645P224RA
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X	± 0.25	ROC PU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR					