




	A	B	C	D	E	F	G				
1	性能参数										
2	1. Heating current: Ui: AC250V, Ith: 20A 发热电流: Ui: AC250V, Ith: 20A			12. Explosion prevention level: IK10 防暴等级: IK10							
3	2. Rated current:16A,AC110V/220V 16A,DC12V/24V 额定电流:16A,AC110V220V 16A,DC12V/24V			13. Working environment temperature: -40 ℃~-+80 ℃ 工作环境温度: -40 ℃~-+80 ℃							
4	3. Power-frequency withstand voltage:1500V/1min 工频耐压:1500V/1min			14. Compression torque: ≤ 4.0N 按压扭力: ≤4.0N							
5	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ			15. Electrical life: 50,000 cycles 电气寿命: 50,000 cycles							
6	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ			16. Mechanical: 500, 000cycles 机械寿命: 500,000cycles							
7	6. Pressing stroke:3.50mm ± 0.10 按压行程:3.50mm ± 0.10			17. Operation method:self-locking 操作方式: 自锁式							
8	7. Contact stroke:1.35mm±0.10 接触行程 :1.35mm±0.10			18. LED lamp power consumption: 20mA以下 LED灯功耗: 20mA以下							
9	8. welding temperature: 320 ℃± 20 ℃ 焊接温度: 320 ℃± 20 ℃			19. LED lamp lifespan: 40000h LED寿命: 40000h							
10	9. Welding duration: Less than 3 seconds in duration 焊接时长: Less than 3 seconds in duration			20. LED color: Red LED颜色: 红色							
11	10. Nut assembly torque:5-14N.m 螺帽装配力矩:5-14N.m			21. LED Lamp Voltage: 24V LED灯电压: 24V							
12	11. Protection level:IP67 防护等级:IP67			22. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N							
13	连接形式										
14	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下										
15	2. Can be used with dedicated connectors: 可配专用接插件使用:										
16	2.1 Switch function wire: Blue wire (NO) (1.0²mm) 开关功能线材: 蓝线 (NO) (1.0²mm)										
17	2.2 LED functional wire: red wire positive pole black wire negative pole(0.5²) LED功能线材: 红线正极 黑线负极 (0.5²)										
18	2.3 LED is an electrodeless lamp bead that can be lit without the need to separate positive and negative poles LED为无极灯珠, 无需分正负极也可点亮										
19	A4				COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
20	A3				X.XX ± 0.10		DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP992203P124RS
21	A2				X.X ± 0.15		DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw
22	A1				X ± 0.25		ROCPO TECHNOLOGY CO.,LTD				
23	REV	DATE	REVISION DESCRIPTION	ISSUE	ANGULAR						
24	A		B		C		D	E	F	G	

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission

A		B		C		D		E		F		G	
材质参数													
9	luminous zone 发光区			PC 塑胶		1							
8	LEDpin LED引脚			Brass 黄铜		1		Silvering 镀银					
7	Base 底座			PBT		1		Silvering 镀银					
6	NOPin NO引脚			Brass 黄铜		1		gold-plating 镀金					
5	Contact material 接触材质			silver alloy 银合金		1		Silvering 镀银					
4	Arm nut 固定螺帽			Brass 黄铜		1		nickeling 镀镍					
3	Oring O型圈			Silica gel 硅胶		1							
2	Housing 外壳			SUS 不锈钢		1							
1	Key 按键			SUS 不锈钢		1							
NO 序号	Part name 部件名			Material 材料		QTY 数量		Remark 备注					

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJCTED		PRODUCT NAME:	
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO:TP992203P124RS	
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw			
A1					ROCPCU TECHNOLOGY CO.,LTD							
REV	DATE	REVISION	DESCRIPTION									
					ANGULAR		—		Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission			

A		B		C		D		E		F		G	
---	--	---	--	---	--	---	--	---	--	---	--	---	--

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission