









	A	B	C	D	E	F		
1				版次 0 1 增加胶芯小缺口, 与小PIN结构保持一致	变更摘要 新产品发行 增加胶芯小缺口, 与小PIN结构保持一致	日期 2015/7/28 2021/9/19		
2					序号 ① ② ③ ④	品名 1.0后压胶芯 (H2.0) 0.5后压端子 (H2.0) 0.5后压后盖 (H2.0) 0.5后压焊片 (H2.0)		
3					材質 LCP UL94V-0 本色 铜合金/表面镀锡 LCP UL94V-0 黑色 铜合金/表面镀锡			
4	技术指标: 1. 塑件表面应光洁、无毛边、无明显收缩、 缺陷、裂纹等现象。 2. 温度范围: -25° C~85° C。 3. 额定电压: 50V, AC/DC(等效)。 4. 接触电阻: ≤0.03 Ω。 5. 绝缘电阻: ≥500MΩ。				CKT 4 5 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22 23 24 25 26 27 28 29 30	DIMA 3.00 4.00 5.00 6.00 7.00 8.00 9.00 10.00 11.00 12.00 13.00 14.00 15.00 16.00 17.00 18.00 19.00 20.00 21.00 22.00 23.00 24.00 25.00 26.00 27.00 28.00 29.00 30.00	DIMB 5.02 6.02 7.02 8.02 9.02 10.02 11.02 12.02 13.02 14.02 15.02 16.02 17.02 18.02 19.02 20.02 21.02 22.02 23.02 24.02 25.02 26.02 27.02 28.02 30.02 31.02	DIMC 8.04 9.04 10.04 11.04 12.04 13.04 14.04 15.04 16.04 17.04 18.04 19.04 20.04 21.04 22.04 23.04 24.04 25.04 26.04 27.04 28.04 29.04 30.04
5					兆星精密电子 (深圳) 有限公司 品名 (TITLE) 1.0间距 2.0高度 后翻盖式 镀金 料号 (DWG.NO) ZX-1.0FPC-2H-HFJ20P 比例 (SCALE) 1:1 单位 (UNITS) mm 张数 (SHEET) 1 OF 1 SIZE A4 REV A	制图 (DR) 校对 (CHKD) 审核 (APPD)		

A

B

C

D

E

F