



[illegible]

|          |                          |   |  |                       |  |           |  |                         |  |   |  |   |  |
|----------|--------------------------|---|--|-----------------------|--|-----------|--|-------------------------|--|---|--|---|--|
| A        |                          | B |  | C                     |  | D         |  | E                       |  | F |  | G |  |
| 材质参数     |                          |   |  |                       |  |           |  |                         |  |   |  |   |  |
| 10       | luminous zone<br>发光区     |   |  | PC<br>塑料              |  | 1         |  |                         |  |   |  |   |  |
| 9        | LEDpin<br>LED脚           |   |  | Brass<br>黄铜           |  | 1         |  | Silvering<br>镀银         |  |   |  |   |  |
| 8        | Base<br>底座               |   |  | PA46                  |  | 1         |  |                         |  |   |  |   |  |
| 7        | Pin<br>引脚                |   |  | Brass<br>黄铜           |  | 1         |  | gold-plating<br>镀金      |  |   |  |   |  |
| 6        | Contact material<br>接触材质 |   |  | silver alloy<br>银合金   |  | 1         |  | Silvering<br>镀银         |  |   |  |   |  |
| 5        | LED Base<br>LED基座        |   |  | PC<br>塑料              |  | 1         |  |                         |  |   |  |   |  |
| 4        | Arm nut<br>固定螺帽          |   |  | Brass<br>黄铜           |  | 1         |  | nickeling<br>镀镍         |  |   |  |   |  |
| 3        | Oring<br>O型圈             |   |  | Silica gel<br>硅胶      |  | 1         |  |                         |  |   |  |   |  |
| 2        | Housing<br>外壳            |   |  | Aluminum alloy<br>铝合金 |  | 1         |  | Oxidized/Black<br>氧化/黑色 |  |   |  |   |  |
| 1        | Key<br>按键                |   |  | Aluminum alloy<br>铝合金 |  | 1         |  | Oxidized/Black<br>氧化/黑色 |  |   |  |   |  |
| NO<br>序号 | Part name<br>部件名         |   |  | Material<br>材料        |  | QTY<br>数量 |  | Remark<br>备注            |  |   |  |   |  |

|     |      |          |             |                                                                                                     |                           |      |            |        |                      |                                                                                       |                         |  |
|-----|------|----------|-------------|-----------------------------------------------------------------------------------------------------|---------------------------|------|------------|--------|----------------------|---------------------------------------------------------------------------------------|-------------------------|--|
| A4  |      |          |             | <br>台普<br>ROCPCU | COMMON TOLERANCE          |      | UNIT       | MM     | PROJECTED            |  | PRODUCT NAME:           |  |
| A3  |      |          |             |                                                                                                     |                           |      | DRAWN BY   | FUYUAN | CHECKED BY           | COCO                                                                                  | MODEL NO: TP91911P224RA |  |
| A2  |      |          |             |                                                                                                     | DATE                      | 2019 | APPROVAL B | ALEN   | Https: www.rocpcu.tw |                                                                                       |                         |  |
| A1  |      |          |             |                                                                                                     | ROCPCU TECHNOLOGY CO.,LTD |      |            |        |                      |                                                                                       |                         |  |
| REV | DATE | REVISION | DESCRIPTION |                                                                                                     |                           |      |            |        |                      |                                                                                       |                         |  |

|                                                                                                                                                          |  |   |  |   |  |   |  |   |  |   |  |   |  |
|----------------------------------------------------------------------------------------------------------------------------------------------------------|--|---|--|---|--|---|--|---|--|---|--|---|--|
| A                                                                                                                                                        |  | B |  | C |  | D |  | E |  | F |  | G |  |
| Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission |  |   |  |   |  |   |  |   |  |   |  |   |  |

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission