





TSSUE DATE	2023. 11. 30	OUR P/N	XR10*12-122K-S 短脚
------------	--------------	---------	-------------------

1. 外观尺寸图 DIMENSIOS



A: 11.5MAX
B: 14.5MAX
C: 4.0 ± 0.5 mm
D: $\phi 0.8 \pm 0.1$ mm
E: 5.0 ± 0.5 mm

2. 接线图 CONNECTION (BOTTOM VIEW)



3. 绕线规格 WINDING SPEC

端子 TERMINZL	线 WIRE	圈数 TURNS	绕线方式 WINDING METHOD
S---F	$\phi 0.28-155^{\circ}\text{C}$	172 TS (REF)	CLOSED

4. 电气特性 ELECTRONICS CHARACTERISTIC

客户代码 Part No.	厂方代码 OUR Part No.	电感量 Inductance at 1KHz	直流电阻 D. C. R max.	定格电流 I. D. C max.	标识 Marking	规格代码 Sample No.
	XR10*12-122K	$1.2\text{mH} \pm 10\%$	—	—	—	—

备注:

OPERATING TEMP. : $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$

INDUCTANCE DROP=10% TYP. AT IDC.

制作 DRW	审核 CHK	确认 APPD
洪碧华 30-11-2023	关菊花 30-11-2023	刘丰 30-11-2023



东莞市祥如电子有限公司
DONGGUAN XIANGRU ELECTRONICS CO., LTD

试产 (样) 报告

(TEST REPORT)

MODEL NO: 产品型号:	XR10*12-122K-S 短脚	EVALUATED Q' TY: 试样数:	10PCS
--------------------	-------------------	--------------------------	-------

WATERIAL CODE: 磁材型号规格:	DR10.0*12.0	TESTED DATE: 试制日期:	2023.11.30
---------------------------	-------------	-----------------------	------------

SPC 规格	L (mH)	1.2mH ± 10%							
			LOTS 序号						
1	1.15								
2	1.24								
3	1.25								
4	1.12								
5	1.25								
6	1.23								
7	1.25								
8	1.2								
9	1.2								
10	1.23								
11									
12									

(DATA)
试样情况记录

REMARK: HM2801A HM2770A HP4342A VR-114 VR115

备注: 1KHz 0.25V

外观. 包装: 外套黑色PVC套管Φ10, 印字(黑色)

RESULTS: 判定:	制样员DRW	
<input checked="" type="checkbox"/> 合格 (PASSED) <input checked="" type="checkbox"/> ROHS	洪碧华	
<input type="checkbox"/> 不合格, 改良后 (FAILED) 参照 (REF) _____	2023.11.30	