






A		B		C		D		E		F		G	
材质参数													
10	luminous zone 发光区			PC 塑料		1							
9	LEDpin LED脚			Brass 黄铜		1		Silvering 镀银					
8	Base 底座			PA46		1							
7	Pin 引脚			Brass 黄铜		1		gold-plating 镀金					
6	Contact material 接触材质			silver alloy 银合金		1		Silvering 镀银					
5	LED Base LED基座			PC 塑料		1							
4	Arm nut 固定螺帽			Brass 黄铜		1		nickeling 镀镍					
3	Oring O型圈			Silica gel 硅胶		1							
2	Housing 外壳			Aluminum alloy 铝合金		1		Oxidized/Black 氧化/黑色					
1	Key 按键			Aluminum alloy 铝合金		1		Oxidized/Black 氧化/黑色					
NO 序号	Part name 部件名			Material 材料		QTY 数量		Remark 备注					

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:		
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91912P224RA5150		
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw				
A1					ROCPCU TECHNOLOGY CO.,LTD								
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR		Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission					
A		B		C		D		E		F		G	



	A	B	C	D	E	F	G
1	性能参数 1.L1-导线长度：默认150MM长； 2.L2-线头长度：默认10MM 3.L3-剥头长度：默认3MM 4.S-导线导体横截面积：默认0.5平方MM、可选0.3平方MM 5.线型拉力N：（0.15-0.25MM）≤30N、（0.3MM）≤40N、（0.5MM）≤50N、（0.75MM）≤60N 6.需要其他线长、线型、可以定制						
2	材质参数 1.插壳：浅蓝色尼龙胶壳 2.端子：磷铜y镀锡色 3.导电线材：紫铜						
3	线束使用说明 1.2线：用于单色的指示灯、无开关功能 2.3线：用于双色指示灯、无开关功能 3.4线：用于三色灯的指示灯、无开关功能 4.3线：用于1NO/1NO1NC开关、无指示灯功能 5.6线：用于2NO/2NO2NC开关、无指示灯功能 6.5线：用于1NO/1NO1NC、单色指示灯带开关功能 7.8线：用于2NO/2NO2NC、单色指示灯带开关功能 8.6线：用于1NO/1NO1NC、双色指示灯带开关功能 9.7线：用于1NO/1NO1NC、三色或220v双色指示灯带开关功能						
5	A4				台普 ROCPCU COMMON TOLERANCE UNIT MM PROJECTED  PRODUCT NAME: DRAWN BY FUYUAN CHECKED BY COCO MODEL NO: TP91912P224RA5150 DATE 2019 APPROVAL B ALEN Https: www.rocpcu.tw ROCPCU TECHNOLOGY CO.,LTD Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission		
	REV	DATE	REVISION	DESCRIPTION	ISSUE		
	A	B	C	D	E	F	G

19MM系列双排单色按钮开关接线说明



接线说明:

- 1、供电电源的正极、按钮开关左边的C脚，接一起。
- 2、供电电源的负极，按钮开关右边的C脚，接一起。
- 3、设备的正极，按钮开关的左NO脚、按钮开关的LED正极，并接一起。
- 4、设备的负极，按钮开关的右NO脚、按钮开关的LED负极，并接一起

实现功能:

- 1、按钮开关**按下去**时：设备正负极都**通电**，按钮开关LED**灯亮**。
- 2、按钮开关**按回去**时：设备正负极都**断电**，按钮开关LED**灯灭**。

注：说明图的电压为接线参考使用，电源电压根据实际供电电压为准。

红线为正极（火线）
黑线为负极（零线）

A4				 台 普 ROCPCU	COMMON TOLERANCE	UNIT	MM	PROJECTED		PRODUCT NAME:
A3						DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO:
A2					X.XX	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE	X					
					ANGULAR	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission				