




REVISION	DESCRIPTION	DATE	DRAFTER
A0	NEW RELEASE	17.12.06	FUYONG.LIU

6	COUPLING NUT	BRASS, Ni-PLATED,50u" MIN.	1	---
5	SEALING GASKET	Si-RUBBER,RED	1	---
4	SNAP RING	BRASS, Ni-PLATED,50u" MIN.	1	---
3	OUTER CONDUCTOR	BRASS, Ni-PLATED,50u" MIN.	1	---
2	INSULATOR	PTFE, WHITE	1	---
1	CENTER CONTACT	MALE, BRASS, Au-PLATED,3u" MIN.	1	---
No.	PART NAME	SPECIFICATION DESCRIPTION	Q'TY	REMARKS

GENERAL TOLERANCE: LINEAR: X ±0.20 X.X ±0.15 X.XX ±0.05 X.XXX ±0.01 ANGLE: X° ±4.00° X.X° ±3.00° X.XX° ±2.00° X.XXX° ±1.00°		HJ-Tech 东莞市皇捷通讯科技有限公司		
FILE NAME: 产品图		TITLE: 射频连接器组件		
ENG/DATE: FUYONG.LIU/17.12.06		SMA公头公针 FOR ANTENNA H8.0*L15.0*OD6.00mm, 主体黄铜镀镍,公针镀金		
CHE/DATE:		P/N: 2LC15PM010		
APP/DATE:		UNIT: mm	SCALE: 1:1	REVISION: A0
				SHEET: 1/1

1.Electrical Characteristics

- 1.1 Impedance:50 Ohm
- 1.2 Working Frequency:DC-6GHz
- 1.3 Working Voltage:335V/max
- 1.4 Insulation Resistance:5000 M ohm

2.Environmental

- 2.1 Working Temperature Range: -40C°~+80C°

COMPLIANCE WITH THE REQUIREMENT: ☒RoHS; ☐HF; ☐SONY SS-00259; ☐OTHERS
*NO USING ESTRICTED AND BANNED SUBSTANCE