

A






B

C

D

E


F



2~3P结构样式

4P 结构样式

版次	变更摘要	日期
0	新产品发行	2018/09/16
1	2P/3P卡扣尺寸由3.0mm变更为3.2mm, 避空公头干涉	2021/11/15



技术指标:

- 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
- 工作温度: -25° C ~ 85° C.
- 额定电压: 250V DC/AC(rms).
- 额定电流: 3.0A AC, DC.
- 接触电阻: ≤ 20mΩ.
- 耐压值: 800V AC/minute.
- 绝缘电阻: ≥ 1000MΩ.
- 产品料号:

WB200AL—** * *—DP
 NO OF CKT(产品PIN数) ——— DP 成品DIP型
 Plating(电镀方式) ——— DP 无LOGO
 Packing(包装方式)
 4: 端子全亮锡 T: TUBE管装
 P: 袋装

CKT	DIM A	DIM B	DIM C
2*2	2.0	6.0	3.2
2*3	4.0	8.0	3.2
2*4	6.0	10.0	3.0
2*5	8.0	12.0	5.0
2*6	10.0	14.0	7.0
2*7	12.0	16.0	9.0
2*8	14.0	18.0	11.0
2*9	16.0	20.0	13.0
2*10	18.0	22.0	15.0
2*11	20.0	24.0	17.0
2*12	22.0	26.0	19.0
2*13	24.0	28.0	21.0
2*14	26.0	30.0	23.0
2*15	28.0	32.0	25.0
2*16	30.0	34.0	27.0
2*17	32.0	36.0	29.0
2*18	34.0	38.0	31.0
2*19	36.0	40.0	33.0
2*20	38.0	42.0	35.0
2*21	40.0	44.0	37.0
2*22	42.0	46.0	39.0

深圳市虹成电子有限公司

品名 (TITLE)	制图 (DR)
2.00 Pitch A型双排直插WTB	Anlan
校对 (CHKD)	李绍宗
料号 (DWG.NO)	审核 (APPD)
HC-PHB2.0-2x5A	黄志明
比例 (SCALE)	张数 (SHEET)
1:1	SIZE
单位 (UNITS)	REV
mm	A
1 OF 1	A4