

# Kinghelm®

| REVISIONS |        |             |     |     |      |
|-----------|--------|-------------|-----|-----|------|
| REV       | NUMBER | DESCRIPTION | DWN | CHK | DATE |
| A         |        | DESIGN      |     |     |      |
|           |        |             |     |     |      |

50±5mm

J1

J2

同向

②

①

②

NOTES:

1. ELECTRICAL:
  - 1.1. VOLTAGE RATING: 60V AC RMS.
  - 1.2. FREQUENCY RANGE: DC 3GHZ
  - 1.3. VSWR: 1.3 MAX.
  - 1.4. CHARACTERISTIC IMPEDANCE: 50 OHMS
2. MATERIAL SEE TABLE:
3. ALL COMPONENTS ARE RoHS COMPLIANT.


| ITEM NO. | PART NUMBER | DESCRIPTION        | QTY. |
|----------|-------------|--------------------|------|
| ②        | 端子          | 高仿 0.81 一代端子, 镀金   | 2    |
| ①        | 线材          | 0.81红色同轴线, OD:0.81 | AS   |

深圳市金航标电子有限公司

www.kinghelm.com.cn

型号: KH-IPEX-IPEX-RG0.81-R50

0755-83044319

|   |  |       |             |                           |      |
|---|--|-------|-------------|---------------------------|------|
| ALL DIMENSION ARE IN MM   | DRAWN  | Jamy  | DATE        | TITLE<br>一代端子, 同向, 总长50MM |      |
|   | ENG.   | Ellis | 2018 /06/22 |                           |      |
| COMPUTER GENERATED IN SOLIDWORKS<br>DO NOT SCALE THIS DRAWING                                       | MFG.   | Alan  | 2018 /06/22 | SIZE Number<br>B          |      |
|   | Q.A.   | Jeff  | 2018 /06/22 |                           |      |
| PROJECTION<br> | GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX<br>±1' ±0.3 ±0.25 ±0.150 |       |             | SCALE: Free               | TYPE |
| CUSTOMER P/N:   |  |       |             | SHEET1 OF 1               |      |