








RoHS

CAD GENERATED DRAWING. DON'T CHANGE BY HAND.

REV.	ECN. NO.	APPD.



CIRCUIT DIAGRAM



PCB WELDING DRAWING

Specification

Operating Life	100,000
Contact rating	50mA@12V DC.
Insulation resistance	1011Ω min.
Contact resistance	100mΩ max.initial.
Dielectric Strength	250 V AC(1mm)
Travel	0.25±0.15mm
Storage Temperature	-30° C to 80° C

Mechanical

ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR
E	Button	Silica	1	Pickling
D	COVER	Stainless Steel	1	Cleaning
C	DOVE	Stainless Steel	1	Plated Ag
B	HOUSING	PPA	1	Black
A	PIN	PHOSPHOR BRONZE	1	Plated Ag

Type	Operating Force(gf)	Height mm	Button	Leads Shape (G, J, D)	Ground pin (0, 1)	Pegs (Optional) (0, 1)
BTS0E005	4	400±50	D	5.0	E (Ecru) U (Bale) V (White)	G 0 (None) 0 (None)
	3	250±50	C	4.3		
	2	160±50	B	3.5		
	1	100±50	A	3.1		

X. ±0.50	X.° ±2°
.X ±0.30	.X° ±1°
.XX ±0.10	.XX° ±0.5°
.XXX ±0.05	

UNITS	mm
MAT'L	
FINISH	
Q'TY	



东莞市博众电气有限公司
Dongguan Bozhong Electrical Co., Ltd

PART NO.
BTS0E005

TITLE:
TACTILE SWITCH 6x6mm

APPD: ROGER

DWG NO.:

BTS0E005

CHKD: ROC



DR: BILLY WANG 2020/08/21

Packaging:
Reel of 1,500 pieces for 3.1-3.5H
Reel of 1,000 pieces for 4.3-5.0H.

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF Bozhong
TECHNOLOGY CO.,LTD
AND SHALL NOT BE REPRODUCED.