




RoHS

CAD GENERATED DRAWING. DON'T CHANGE BY HAND.

REV.	ECN. NO.	APPD.



CIRCUIT DIAGRAM



PCB WELDING DRAWING

Specification

Operating Life	100,000
Contact rating	50mA@12V DC.
Insulation resistance	1011Ω min.
Contact resistance	100mΩ max. initial.
Dielectric Strength	250 V AC(1mm)
Travel	0.2±0.1mm
Storage Temperature	-30° C to 80° C

E	Button	PPA	1	White
D	COVER	Phosphor copper	1	Silver
C	DOVE	Stainless Steel	1	Plated Ag
B	HOUSING	PPA	1	Black
A	Cards	Phosphor copper	1	Plated Ag
ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR

Mechanical

P/N	Operating Force(gf)	Height mm	Button Shape (L, T)	Lead shape (L, T)	Ground pin (0, 1)	Page Option (0, 1)
BTS0B008	3	300±50		B(Black) W(White)	G	0 (None)
	2	250±50	B	2.7		
	1	180±50	A	2.5		

X.	±0.50	X.°	±2°
.X	±0.30	.X°	±1°
.XX	±0.10	.XX°	±0.5°
.XXX	±0.05		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF Bozhong TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED.

UNITS	mm
MAT'L	
FINISH	
Q'TY	

 东莞市博众电气有限公司 Dongguan Bozhong Electrical Co., Ltd	
PART NO. BTS0B008	TITLE: TACTILE SWITCH 3x6mm
APPD: ROGER	DWG NO.: BTS0B008
CHKD: ROC	
DR: BILLY WANG 2020/08/21	
	

Packaging:
a reel of 3,000 pieces.