






CAD GENERATED DRAWING. DON'T CHANGE BY HAND.

REV.	ECN. NO.	APPD.



CIRCUIT DIAGRAM



PCB WELDING DRAWING

Specification

Operating Life	100,000
Contact rating	50mA@12V DC.
Insulation resistance	1011Ω min.
Contact resistance	100mΩ max.initial
Dielectric Strength	250 V AC(1mm)
Travel	0.15±0.1mm
Storage Temperature	-30° C to 80° C

Packaging:
a reel of 5,000 pieces

C	DOVE	Stainless Steel	1	Plated Ag
B	HOUSING	LCP	1	Black
A	CARDS	Phosphor copper	1	Plated Ag
ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOUR

Mechanical

P/N	Operating Force (gf)	Height (mm)	Button	Leads Shape (6x, 1.7)	Ground pin (0, 1)	Page Option (0, 1)
BTSOC003	2	250±50				
	1	180±50	A	0.8		

X. ±0.50	X. ° ±2°
.X ±0.30	.X ° ±1°
.XX ±0.10	.XX ° ±0.5°
.XXX ±0.05	

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF Bozhong TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED.

UNITS mm	 东莞市博众电气有限公司 Dongguan Bozhong Electrical Co., Ltd
MAT'L	PART NO. BTSOC003
FINISH	APPD: ROGER
Q'TY	CHKD: ROC
	DR: BILLY WANG 2020/08/21
	TITLE: TACTILE SWITCH 4.8x4.8x0.8
	DWG NO.: BTSOC003
	