




P. C. B LAYOUT




■ SPECIFICATIONS

- Voltage rating: 600V AC, DC
- Current rating: 7A, AC, DC
- Withstanding Voltage: 1500V AC/minute
- Insulation resistance: 1000MΩ min
- Temperature range: -40° C~+105° C
- Contact resistance: 20mΩ max

■ WAFER

- Part No.: CS-1150R-2xXXDZV2WG
- Poles : 02-24P
- Housing Material: Nylon66 UL94V-0(白色)
- Pin Material: Brass
- Contact Area Plating: Gold Flash (镀金)
- The Dimension Marked “▼” Must Be Recorded



CIRCUIT SIZE LAYOUT

PART NO.	Dimensions (mm)	
	A	B
2x01	—	5.60
2x02	4.20	9.80
2x03	8.40	14.00
2x04	12.60	18.20
2x05	16.80	22.40
2x06	21.00	26.60
2x07	25.20	30.80
2x08	29.40	35.00
2x09	33.60	39.20
2x10	37.80	43.40
2x11	42.00	47.60
2x12	46.20	51.80

RoHS2.0

本图纸知识产权及版权由深圳市永丰盈电子有限公司所有,未经书面许可不准擅自传阅、复制和修改. 本公司保留法律追究的权利。

类别	WAFER	料号	CS-1150R-2xXXDZV2WG		
版本	A/0	设计	LIWENCHANG	X.X	±0.40
制定部门	工程部	绘制	LIWENCHANG	X.XX	±0.30
工程图号		审核	ZHOZHONGHU	X.XXX	±0.20
制定日期	2022/12/13	核准	LIZENGCAI	X.XXXX	±0.10

材料		单位	mm
颜色		比例	1:1
画法		数量	
CST 深圳市永丰盈电子有限公司 ShenZhenYongFengYing ELEETRONICS CO.,LTD.			

SHEET 1 OF 1		
	修改内容	修改日期