




P.C.B LAND DIMENSION





NOTES:

- 1.Rating:12VDC 50mA
- 1.额定值: 12VDC 50mA
- 2.Dielectric Strength:250V AC
- 2.耐电压: 250V AC
- 3.Contact Resistance:≤100mΩ Max
- 3.接触电阻: ≤100mΩ
- 4.Insulation Resistance:≥100MΩ
- 4.绝缘电阻: ≥100MΩ
- 5.Working temperature: -40℃~+80℃
- 5.工作温度: -40℃~+80℃
- 6.Stroke: 0.40 ± 0.20mm
- 6.行程: 0.40±0.20mm
- 7.Waterproof grade: IP67
- 7.防水等级: IP67
- 8.Operating Force:160±80gf
- 8.操作力: 160±80gf
- 9.Life: 300,000 times
- 9.寿命: 300,000 次



CIRCUIT DIAGRAM



6	Stem 按钮	LCP	1	Black 黑色
5	Cover 盖板	SUS	1	
4	Plunger 垫片	RUBBER	1	Sky Blue 天蓝色
3	Shrapnel 弹片	SUS	1	Ag plating 镀银
2	Pedestal 基座	PA6T	1	Black 黑色
1	Terminal 端子	Brass	1	Ag plating 镀银
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:					
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP14321672					
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw					
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD									
					X	± 0.25										
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission									
				A		B		C		D		E		F		G