

订货规则

全新客户定制编号规则

NEW CUSTOM NUMBERING RULES

M12 - P 8 A - G W A P7 - 1 PV -S

系列号(Serie):

M5、M8、M9、M12、M16、M623、M923、7/8等

M5、M8、M9、M12、M16、M623、M923、7/8等

公母(Male & Female):

P: 针型 S: 孔型

P: Male type S: Female type

芯数(Contacts number):

2、3、4、5、6、7、8、12、14、16、17、19、21、24等

2、3、4、5、6、7、8、12、14、16、17、19、21、24等

接口型号(Code):

A、B、C、D、K、L、M、S、T、Y、X等

A、B、C、D、K、L、M、S、T、Y、X等

材质(Material quality):

G: 金属插座/插头(Metal socket/plug)

P: 塑料插座/插头(Plastic socket/plug)

M: 成型式插头(Formed plug)

接线方式(Connection):

W: 焊接(Welding)

P: 插接(Insertion)

S: 贴片(Patch)

L: 螺钉(Screw)

C: 压接(Crimping)

T: 穿孔(Through-hole)

结构(Structure):

A: 直式插头(Straight plug)

D: 弯式插头(Curved plug)

B: 板前安装插座(Installation socket in front of the board)

F: 板后安装插座(Installing sockets behind the board)

H: 方形法兰插座(Square flange socket)

L: 弯针插座(Curved pin socket)

S: 贴片式插座(SMD socket)

O: 终端电阻插头(Terminal resistor plug)

屏蔽(Shield):

-S: 有屏蔽

空: 无屏蔽

-S: Shielded

Empty: No shielding

线材(Cable material):

PV: PVC

PU: 包含TPU和PUR(TUP and PUR)

TF: 铁氟龙(PTFE)

PE: PE

线长(Cable length):

以(M)米为单位

In (M) meters

尾部出线口与板端螺口:

(Tail outlet & Plate end screw mouth):

O8: ϕ 8mm

P7: PG7

M12: M12

.....等