








1	2	3	4	5	6	7	8
版本	变更内容		工程确认	日期			



适用扁平线 (Applicable Flat Cable)

CKT	DIMA	DIMB	DIMC
2	1.00	3.10	6.90
3	2.00	4.10	7.90
4	3.00	5.10	8.90
5	4.00	6.10	9.90
6	5.00	7.10	10.90
7	6.00	8.10	11.90
8	7.00	9.10	12.90
9	8.00	10.10	13.90
10	9.00	11.10	14.90
11	10.00	12.10	15.90
12	11.00	13.10	16.90
13	12.00	14.10	17.90
14	13.00	15.10	18.90
15	14.00	16.10	19.90
16	15.00	17.10	20.90
17	16.00	18.10	21.90
18	17.00	19.10	22.90
19	18.00	20.10	23.90
20	19.00	21.10	24.90
21	20.00	22.10	25.90
22	21.00	23.10	26.90
23	22.00	24.10	27.90
24	23.00	25.10	28.90
25	24.00	26.10	29.90
26	25.00	27.10	30.90
27	26.00	28.10	31.90
28	27.00	29.10	32.90
29	28.00	30.10	33.90



适用线路板 (PCB LAYOUT)

- 技术指标:
- 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
 - 温度范围: -25° C~85° C.
 - 额定电压: 50V, AC/DC(等效).
 - 接触电阻: ≤0.03Ω.
 - 绝缘电阻: ≥500MΩ
 - 产品料号:

BTC10202-*** ** *-***
 NO OF CKT (产品PIN数) 00 看盖有LOGO:WD
0# 看盖无LOGO
 Plating(电镀方式) Packing(包装方式)
 0:端子全雾锡 T:TUBE管装
 1:端子全金(G/F OVERALL) R:TAPE & REEL卷装
 5:端子半金锡

序号	品名	材质
①	0.5mm盖胶芯 (H2.0)	LCP UL94V-0 本色
②	0.5mm盖端子 (H2.0)	铜合金/表面镀锡
③	0.5mm盖后盖 (H2.0)	LCP UL94V-0 黑色
④	0.5mm盖焊片 (H2.0)	铜合金/表面镀锡

东莞市博众电气有限公司 Dongguan Bozhong Electrical Co., Ltd	页码 (SHEET)	1/1	单位(UNIT): MM
	版本 (REV)	A1	比例(SCALE)
品名 (ITEM NO)	1.0 Pitch掀盖卧式下接 (H=2.0)	日期 (DATE)	2021. 10. 12
料号 (PART NO)	BTC10202-****-**XW	设计 (DESIGN)	LUO
图号 (DWG NO)		审核 (CHECKED)	ROGER LI
		核准 (APPROVED)	ROC ZHAO

These drawings and specifications are Dongguan Bozhong Technology Co Ltd. The property should not be copied. Without Dongguan Bozhong Technology Co. Ltd. Prior written consent to copy or use in any way. Email at info@bozhongelectric.com