



受控文件章

Electrical character:

- a. 100% open & short testing;
- b. Withstanding voltage: DC 300V 0.01Sec;
- c. Insulation resistance: $5M\Omega$ (Min);
- d. Conductive resistance 3Ω (Max).
- e. 严格控制好分线紧挨线夹，不可过长，以免影响信号传输。
- f. 电脑实测传输数据10G.

外被
编织
部品一
部品二
部品三
部品四
部品五

CABLE SPECIFICATION

4	TPE胶料	10g	J2-401101	黑色 PVC 40P
3	PE胶料	3g	J4-111105	PE 胶料
2	3.1 Type C	2Pcs	C4-11CC01	3.1TYPE C C2M拉伸氨镍端子C5191镀金1u黑胶3.1 C-C无IC CI=10nf
1	Cable	1M	X4-482421	USB 3.1 (32#*4P+A)*4C+32#*1P+32#*4C+24#*2C+48铜编 0D4.8 黑色雾面PVC
No.	DESCRIPTION	QTY.	PART NUMBER	DETAIL
TOLERANCE		APPROVALS	DATE	TITLE
X X.X X.XXX	+0.5 ±0.3 ±0.20 ±0.10	DRAWN CHECKED APPROVED	ALEX 28/10/2022	USB3.1 C to C(TYPE C)长 模具UC33) 数据线 黑色 1 米 (US31IN1001-CTC)
ANGULAR ±1°		PHOTO	11.8	UNIT mm
(UNLESS OTHERWISE SPECIFIED)		ENG DWG	PHD	SIZE A4
				SCALE /
				SHEET 1/1
				DWG No. 424481-100CC11
				US31IN1001-CTC
				REV. 00
广东联德普特电子有限公司				