



6

未经允许禁止传播、复制、编辑或入档，以及利用其内容进行交流

注:



Pitch Range In mm		Nominal Dimension In mm		Range						
Over 6 TO 10	Over 10 TO 24	Over 30 TO 60	Over 60 TO 100	Over 100 TO 150	Over 150	0.1/10	—	∩	□	
±0.15	±0.20	±0.30	±0.50	±0.70	±1.00	±1.30	±2°			

	2		1	
REV	ECN NO.	CONTENT	CHK	DATE

NOTES:

UL Standard

UL Standard

Use group	B	C	D
Rated Current	15A	/	10A
Rated Voltage	300V	/	300V

2. Torque value: M2.5, 3.54Lb.in

3. Wire range: 28~12AWG

IEC Standard

Pollution Degree	3	2	2
Overvoltage Category	III	III	II
Rate Impulse Voltage(KV)	/	4.0KV	/
Rate Voltage(V)	/	400V	/
Rate Current(A)	/	15A	/

2. Torque value: M2.5, 0.4Nm

3. wire range: 0.2~2.5mm²

NOTES:

- 1.Housing: PA66 (UL94V-0)
- 2.Cover: PA66 (UL94V-0)
- 3.Cage: Brass (Ni Plated)
- 4.Clamp: Copper alloy (Ni Plated)
- 5.Screw: Steel (M2.5,Zn Plated)

NOTES:

- 1.Pitch: 7.62mm Poles: 02-24P

3. Operating temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$

How to order

MX2EDGK - 7.62 - XXP - XXXX - X - X - X

— A-Z 其他定制

灰色:GY 橙色:OE 02-99:

蓝色:BU 红色:RD 定制颜色

黒色:BK 鍵顏色:

白色:W 2.F.3 | 大 | 寸 紫

EW: 斜古押

永邑: QN 吳邑: I W
永明邑: TT 台邑: V/E

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG.	CKK	DATE 23.06.20	UNITS	MM	SHEET/OF 1/1
G/K.		DATE	SCALE	1 : 1	A4 
APP.		DATE	NAME	MX2EDGK-7.62-XXP	
 CIX MAXXU ELECTRONICS CO.,LTD. 慈溪市近旭电子有限公司			DWGNO		