







REV(版本)	DESCRIPTION(描述)	NAME(名字)	DATE(日期)



CKT	Dim A	Dim B	Dim C
2	1.50	6.00	3.65
3	3.00	7.50	5.15
4	4.50	9.00	6.65
5	6.00	10.50	8.15
6	7.50	12.50	9.65
7	9.00	13.50	11.15
8	10.50	15.50	12.65
9	12.50	16.50	14.15
10	13.50	18.50	15.65
11	15.50	19.50	17.15
12	16.50	21.50	18.65
13	18.50	22.50	20.15
14	19.50	24.50	21.65
15	21.50	25.50	23.15
16	22.50	27.50	24.65
17	24.50	28.50	26.15
18	25.50	30.00	27.65
19	27.50	31.50	29.15
20	28.50	33.00	30.65

技术指标:

- 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
- 温度范围: -40° C~85° C.
- Working temp: -40° C~85° C.
- 额定电压: 100V, AC/DC.
- Voltage rating: 100V AC/DC(cms)
- 接触电阻: ≤40mΩ.
- 绝缘电阻: ≥500MΩ.
- Insulation resistance: 500MΩ min
- 额定电流: 2A, AC/DC.
- Current rating: 2A AC/DC
- 耐电压: AC 500V/1分钟
- Withstanding Voltage: 500V AC/minute
- PIN保持力: 10N min
- pin Retention Force: 10N min
- 主体材料: LCP UL94-V0, 本色
- Housing material: LCP UL94-V0, 本色
- 端子材料: 黄铜C2680, 镀镍50u" min, 镀亮锡100u" min
- Terminal material: Brass C2680, plating Ni 50u" min, plating Tin 100u" min
- 焊片材料: 黄铜C2680, 镀镍50u" min, 镀亮锡100u" min
- Solder tab material: Brass C2680, plating Ni 50u" min, plating Tin 100u" min

12. 标有“▽”为重点管控

MAJOR DIMENSION: ▽

深圳市连欣科技有限公司

品名 (TITLE)	制图 (DRT)	X1A0
Pitch: 1.50mm ZH 卧式 SMT	校对 (CHKD)	Alex

料号 (PART NO)	审核 (APP)	
XDWF-0151WT-**P		

比例 (SCALE)	单位 (UNITS)	页码 (SHEET)	尺寸 (SIZE)	版本 (REV)
1:1	mm	1 OF 1	A4	A

一般公差 (TOLERANCE)
X ±0.50 XX ±1.0
X ±0.20 XXX ±0.05
ANGLES ±1°