

6

注: 未经允许禁止传播、复制、编辑或入档, 以及利用其内容进行交流

		2		1	
REV	E.C.N NO.	CONTENT	CHK	DATE	

NOTES:

UL Standard

Use group	B	C	D
Rated Current	15A	/	10A
Rated Voltage	300V	/	300V

2.withstanding voltage: AC1600V/1Min

IEC Standard

Pollution Degree	3	2	2
Overvoltage Category	III	III	II
Rate Impulse Voltage(kV)	/	4.0kV	/
Rate Voltage(V)	/	400V	/
Rate Current(A)	/	15A	/



NOTES:

- 1.Housing: PA66 (UL94V-0)
- 2.Solder Pin: Brass (Sn Plated)

NOTES:

- 1.Pitch: 7.62mm Poles: 02-24P
2.Operating temperature: -40°C~+105°C
3.RoHS Compliance

How to order



Pitch Range		In	Nominal Dimension Range					— ∩ ∇		
mm			In mm							
Over	Over	Over	Over	Over	Over	Over	Over	0.1/10		
6	10		30	60	100	150				
TO	TO		TO	TO	TO					
6	10	24	30	60	100	150		≤		
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30			

ITEM	NAME OF PART	NO. OF PART	Q-TY	MATERIAL	NOTE
DWG.	CKK	DATE	23.06.20	UNITS	MM
CHK.		DATE		SCALE	1 : 1
APP.		DATE			A4
					
 CIXI MAIXU ELECTRONICS CO.,LTD. 慈溪市迅旭电子有限公司			NAME	MX2EDGRC-7.62-XXP	
			DWGNO		