






REV(版本)	DESCRIPTION(描述)	NAME(名字)	DATE(日期)


### 2P 结构



- 技术指标:
1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
  2. 温度范围: -40° C~85° C.
  3. 额定电压: 250V, AC/DC.
  4. 接触电阻: ≤20mΩ.
  5. 绝缘电阻: ≥1000MΩ.
  6. 额定电流: 4A, AC/DC.



CKT	Dim A	Dim B	Dim C
2	2.50	7.50	10.00
3	5.00	10.00	12.50
4	7.50	12.50	15.00
5	10.00	15.00	17.50
6	12.50	17.50	20.00
7	15.00	20.00	22.50
8	17.50	22.50	25.00
9	20.00	25.00	27.50
10	22.50	27.50	30.00
11	25.00	30.00	32.50
12	27.50	32.50	35.00
13	30.00	35.00	37.50
14	32.50	37.50	40.00
15	35.00	40.00	42.50
16	37.50	42.50	45.00



序号	项目	描述	备注
1	塑胶	LCP	
2	端子	黄铜	
3	焊片	黄铜	

一般公差 (TOLERANCES)  
 X ± 0.10 XX ± 0.15  
 Y ± 0.20 ZXX ± 0.05  
 ANGLES ±1°

深圳市连欣科技有限公司

品名 (TITLE)	制图 (DR)	XIAO
Pitch: 2.54mm 卧式 SMT	校对 (CHKD)	Alex
料号 (DMG.NO)	审核 (APPD)	
XDFW-2500-**P	比例 (SCALE)	1:1
单位 (UNITS)	页码 (SHEET)	1 OF 1
mm	尺寸 (SIZE)	A4
	版数 (REV)	A