





注：本板为禁止传输、复制、编辑、修改、以及利用其内容进行交流



PCB Layout

REV	EC.N NO.	CONTENT	CHK	DATE
-----	----------	---------	-----	------

NOTES1:

UL Standard

1. Use group	B	C	D
Rated Current	15A	/	10A
Rated Voltage	300V	/	300V

2. withstanding voltage: AC1600V/1Min

IEC Standard

1. Pollution Degree	3	2	2
Overvoltage Category	III	III	II
Rate Impulse Voltage(KV)	/	4.0KV	/
Rate Voltage(V)	/	400V	/
Rate Current(A)	/	15A	/

NOTES2:

1.Housing: PA66 (UL94V-0)

2.Solder Pin: Brass (Sn Plated)

NOTES3:

1.Pitch: 7.62mm Poles: 02-24P

2.Operating temperature: -40℃~+105℃

3.RoHS Compliance

How to order

MX2EDGV - 7.62 - XXP - XXXX - X - X
产品型号 间距 极数 颜色: 01:常频颜色 02-99: A-Z其他定制

颜色: 灰色:GY 橙色:OE 定制颜色
蓝色:BU 红色:RD
黑色:BK 透明色:TT
绿色:GN 黄色:YW
透明色:TT 白色:WE

Cu 铜
Fe 铁

Pitch Range In mm	Nominal Dimension In mm	Range	-	□
Over 6 TO 10	Over 10 TO 24	Over 30 TO 60	Over 60 TO 100	Over 100 TO 150
TO 6 TO 10	TO 24 TO 30	TO 60 TO 100	TO 100 TO 150	TO 150 TO 300
±0.15	±0.20	±0.30	±0.50	±0.70
±0.20	±0.30	±0.50	±0.70	±1.00
±0.30	±0.50	±0.70	±1.00	±1.30
±0.50	±0.70	±1.00	±1.30	±2"

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG.	CHK	DATE	23.06.20	UNITS	MM
CHK	DATE	SCALE	1:1	SHEET/OF	1/1
APP.	DATE	NAME	MX2EDGV-7.62-XXP		
CIXI MAIXU ELECTRONICS CO.,LTD					
东莞市迈旭电子有限公司					
DWGNO.					