








RoHS



适用扁平线(Applicable Flat Cable)



Model No.	Pin	DIM A	DIM B	DIM C	DIM D
FPC-0.5LS-04PH20	4	1.50	2.56	7.60	5.20
FPC-0.5LS-05PH20	5	2.00	3.06	8.10	5.20
FPC-0.5LS-06PH20	6	2.50	3.56	8.60	5.20
FPC-0.5LS-07PH20	7	3.00	4.06	9.10	5.20
FPC-0.5LS-08PH20	8	3.50	4.56	9.60	5.20
FPC-0.5LS-09PH20	9	4.00	5.06	10.10	5.20
FPC-0.5LS-10PH20	10	4.50	5.56	10.60	5.20
FPC-0.5LS-11PH20	11	5.00	6.06	11.10	5.20
FPC-0.5LS-12PH20	12	5.50	6.56	11.60	5.20
FPC-0.5LS-13PH20	13	6.00	7.06	12.10	5.20
FPC-0.5LS-14PH20	14	6.50	7.56	12.60	5.20
FPC-0.5LS-15PH20	15	7.00	8.06	13.10	5.20
FPC-0.5LS-16PH20	16	7.50	8.56	13.60	5.20
FPC-0.5LS-17PH20	17	8.00	9.06	14.10	5.20
FPC-0.5LS-18PH20	18	8.50	9.56	14.60	5.20
FPC-0.5LS-19PH20	19	9.00	10.06	15.10	5.20
FPC-0.5LS-20PH20	20	9.50	10.56	15.60	5.20
FPC-0.5LS-21PH20	21	10.00	11.06	16.10	5.20
FPC-0.5LS-22PH20	22	10.50	11.56	16.60	5.20
FPC-0.5LS-23PH20	23	11.00	12.06	17.10	5.20
FPC-0.5LS-24PH20	24	11.50	12.56	17.60	5.20
FPC-0.5LS-25PH20	25	12.00	13.06	18.10	5.20
FPC-0.5LS-26PH20	26	12.50	13.56	18.60	5.20
FPC-0.5LS-27PH20	27	13.00	14.06	19.10	5.20
FPC-0.5LS-28PH20	28	13.50	14.56	19.60	5.20
FPC-0.5LS-29PH20	29	14.00	15.06	20.10	5.20
FPC-0.5LS-30PH20	30	14.50	15.56	20.60	5.20
FPC-0.5LS-31PH20	31	15.00	16.06	21.10	5.20
FPC-0.5LS-32PH20	32	15.50	16.56	21.60	5.20

Model No.	Pin	DIM A	DIM B	DIM C	DIM D
FPC-0.5LS-33PH20	33	16.00	17.06	22.10	5.20
FPC-0.5LS-34PH20	34	16.50	17.56	22.60	5.20
FPC-0.5LS-35PH20	35	17.00	18.06	23.10	5.75
FPC-0.5LS-36PH20	36	17.50	18.56	23.60	5.75
FPC-0.5LS-37PH20	37	18.00	19.06	24.10	5.75
FPC-0.5LS-38PH20	38	18.50	19.56	24.60	5.75
FPC-0.5LS-39PH20	39	19.00	20.06	25.10	5.75
FPC-0.5LS-40PH20	40	19.50	20.56	25.60	5.75
FPC-0.5LS-41PH20	41	20.00	21.06	26.10	5.75
FPC-0.5LS-42PH20	42	20.50	21.56	26.60	5.75
FPC-0.5LS-43PH20	43	21.00	22.06	27.10	5.75
FPC-0.5LS-44PH20	44	21.50	22.56	27.60	5.75
FPC-0.5LS-45PH20	45	22.00	23.06	28.10	5.75
FPC-0.5LS-46PH20	46	22.50	23.56	28.60	5.75
FPC-0.5LS-47PH20	47	23.00	24.06	29.10	5.75
FPC-0.5LS-48PH20	48	23.50	24.56	29.60	5.75
FPC-0.5LS-49PH20	49	24.00	25.06	30.10	5.75
FPC-0.5LS-50PH20	50	24.50	25.56	30.60	5.75
FPC-0.5LS-51PH20	51	25.00	26.06	31.10	5.75
FPC-0.5LS-52PH20	52	25.50	26.56	31.60	5.75
FPC-0.5LS-53PH20	53	26.00	27.06	32.10	5.75
FPC-0.5LS-54PH20	54	26.50	27.56	32.60	5.75
FPC-0.5LS-55PH20	55	27.00	28.06	33.10	5.75
FPC-0.5LS-56PH20	56	27.50	28.56	33.60	5.75
FPC-0.5LS-57PH20	57	28.00	29.06	34.10	5.75
FPC-0.5LS-58PH20	58	28.50	29.56	34.60	5.75
FPC-0.5LS-59PH20	59	29.00	30.06	35.10	5.75
FPC-0.5LS-60PH20	60	29.50	30.56	35.60	5.75

技术指标(Technical Index):

- 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena.)
- 温度范围(Temperature range): -25°C~+85°C.
- 额定电流(Rated current): 0.5A
- 额定电压(Rated voltage): 50V, AC/DC(=等效).
- 耐电压(Withstand Voltage): 500V, AC/minute.
- 接触电阻(Contact resistance): ≤50mΩ.
- 绝缘电阻(Insulation resistance): ≥500MΩ.

①	Soldering lug		1	Phosphor Bronze	Plating Sn
②	Cover		1	LCP	Black
③	Terminal			Phosphor Bronze	Plating Sn
④	Housing		1	LCP	Off White
NO.	Name	Number	Qty	Materil	Remarks

YUANDI® Yuandi Electronics Co., Ltd

design	date	name	FPC CONNECTOR
Review	date	model	FPC-0.5LS-□□PH20
Approved	date		

Drawing number:

Tolerance	not specified	Proportion	1:1	unit	mm	gaps	number	A4
-----------	---------------	------------	-----	------	----	------	--------	----