





注：本板为禁止转输、复制、编辑或存档，以及用其内容进行交流



REV	EC.N NO.	CONTENT	CHK	DATE
-----	----------	---------	-----	------

NOTES1:
UL Standard

1. Use group	B	C	D
Rated Current	15A	/	10A
Rated Voltage	300V	/	300V

2. withstanding voltage: AC1600V/1Min
IEC Standard

1. Pollution Degree	3	2	2
Overvoltage Category	III	III	II
Rate Impulse Voltage(KV)	/	4.0KV	/
Rate Voltage(V)	/	400V	/
Rate Current(A)	/	15A	/

NOTES2:

- Housing: PA66 (UL94V-0)
- Solder Pin: Brass (Sn Plated)

NOTES3:

- Pitch: 7.62mm Poles: 02-24P
- Operating temperature: -40℃~+105℃
- 3RoHS Compliance

How to order

MX2EDGR - 7.62 - XXP - XXXX - X - X
产品型号 间距 极数 01:常规颜色 02-99: A-Z其他定制

颜色: 灰色:GY 橙色:OE 定制颜色
蓝色:BU 红色:RD
黑色:BK 透明色:TT
绿色:GN 黄色:YW
透明色:TT 白色:WE

Cu 铜
Fe 铁

Pitch Range In mm	Nominal Dimension Range In mm	—	□
Over 6 TO 10	Over 30 TO 60	Over 100 TO 150	0.1/10
Over 10 TO 24	Over 60 TO 100	Over 150 TO 150	≤
±0.15 ±0.20	±0.30 ±0.30 ±0.50 ±0.70 ±1.00 ±1.30	±2°	

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG.	CHK	DATE	23.06.20	UNITS	MM
CHK	DATE	SCALE	1:1	SHEET/OF	1/1
APP.	DATE	NAME	MX2EDGR-7.62-XXP		



CIXI MAIXU ELECTRONICS CO., LTD.
慈溪市迈旭电子有限公司

DWGNO.